



**Part Number: 83659**

Audio/Control/Instrumentation, (9) 18 AWG (19x30) TC, FEP/FEP, Foil+TC Braid Shld, CMP

## Product Description

Nine 18 AWG stranded (19x30) tinned copper conductors, plenum, Teflon® (FEP) insulation, overall Beldfoil® shield (100% coverage) plus tinned copper braid shield (85% coverage), Teflon® (FEP) jacket.

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Conductors
18	19x30	TC - Tinned Copper	9

Conductor Count:	9
AWG Size:	18

#### Insulation

Material	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.0065 in

#### Color Chart

Number	Color
1	Black
2	White
3	Red
4	Green
5	Orange
6	Blue
7	White/Black
8	Red/Black
9	Green/Black

#### Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminum Foil-Polyester Tape	Beldfoil®	100 %
Braid	2	TC - Tinned Copper		85 %

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.265 in	0.015 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
5.8 Ohm/1000ft	2.7 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
33 pF/ft	60 pF/ft

#### Inductance

<b>Nominal Inductance</b>
0.14 µH/ft

**Current**

Element	Max. Recommended Current [A]
10C Temperature Rise	3.8 Amps per conductor @ 25°C ambient

**Voltage**

<b>UL Voltage Rating</b>
300V RMS

**Temperature Range**

Operating Temp Range:	-70°C To +200°C
-----------------------	-----------------

**Mechanical Characteristics**

Bulk Cable Weight:	81 lbs/1000ft
Max Recommended Pulling Tension:	216 lbs
Min Bend Radius/Minor Axis:	2.75 in

**Standards**

NEC Articles:	800
NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
CPR Euroclass:	Eca

**Applicable Environmental and Other Programs**

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

**Suitability**

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

**Flammability, LSOH, Toxicity Testing**

UL Flammability:	NFPA 262
CSA Flammability:	FT6

**Part Number**

Plenum (Y/N):	Yes
---------------	-----

**Variants**

Item #	Color	Footnote
83659 002100	RED	
83659 0021000	RED	C
83659 002500	RED	C
83659 0025000	RED	C Z

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.