



**Electrical performance:**  
CEI EN 50393 with connectors  
complying with EN 61238-1  
(with testing under water head and water  
between the cable cores)  
Class 2 in accordance with CEI 64-8.

**Gel:** UL 94-HB 

Operating  
temperature 





Installation temperature:   
-40°C / +50°C

**IPX8**  
OFFICIALLY  
TESTED **IMQ**


# Gel Cover Line

Pre-filled gel accessories for straight connections,  
for the protection, safety and covering of electrical  
connections using strip connectors or alternatives.

- For 3 x 1 to 6 mm<sup>2</sup> cables or 3 insulated wires
- For civil and industrial connections
- To put household systems in order
- Also for underwater use
- Non-toxic and with no shelf life
- Halogen free
- UV resistant



## OHM & BAR




Product	Housed connectors type	Pieces for package	Package type	Dimensions A x B x C (mm)
OHM	2 from 4 mm <sup>2</sup>	1	blister	61 x 35 x 28
OHMp11		11	box	
BAR	3 from 4 mm <sup>2</sup> / 6 mm <sup>2</sup>	1	blister	63 x 41 x 28
BARp9		9	box	



**Ray  
Tech**

## Mammut Gel Cover



Product	Housed connectors type	Pieces for package	Package type	Dimensions A x B x C (mm)
Gel Cover 4	2 from 4 mm <sup>2</sup>	1	blister	61 x 35 x 28
Mammut Gel Cover		8	box	
Gel Cover 6	3 from 4 mm <sup>2</sup> / 6 mm <sup>2</sup>	1	blister	63 x 41 x 28
Mammut Gel Cover 6		6	box	

No flame propagation. CEI 20-35 • IEC 60332-1 • HD405-1 (as applicable). **Casing mix:** UL 94-V2

### Installation examples

