



Part Number: 85220

Control/Instrumentation, (2) 20 AWG (7x28) TC, ETFE/ETFE

Product Description

Two 20 AWG stranded (7x28) tinned copper conductors, Tefzel® (ETFE) insulation, Tefzel® (ETFE) jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
20	7x28	TC - Tinned Copper	2

Conductor Count:	2
Total Number of Pairs:	1
AWG Size:	20

Insulation

Material	Material Trade Name	Nominal Wall Thickness
ETFE - Ethylene Tetrafluoroethylene	Tefzel®	0.015 in

Color Chart

Number	Color
1	Black
2	Red

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness
ETFE - Ethylene Tetrafluoroethylene	Tefzel®	0.185 in	0.02 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
9.3 Ohm/1000ft

Inductance

Nominal Inductance
0.186 µH/ft

Current

Max. Recommended Current [A]
4 Amps per conductor @ 25°C

Voltage

Non-UL Voltage Rating
300 V RMS

Temperature Range

Non-UL Temp Rating:	150°C
Operating Temp Range:	-60°C To +150°C

Mechanical Characteristics

Bulk Cable Weight:	19 lbs/1000ft
Max Recommended Pulling Tension:	28 lbs
Min Bend Radius/Minor Axis:	2 in

Standards

CPR Euroclass:	Eca
----------------	-----

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
------------------	------

Part Number

Plenum (Y/N):	No
---------------	----

Variants

Item #	Color	Footnote
85220 368100	CLEAR, TRANSPARENT	
85220 3681000	CLEAR, TRANSPARENT	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Tefzel is a trademark of Dupont.
--------	----------------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.