



K259 : Shoe and Helmet

re-odourising spray

Description of product

A high quality solvent based aerosol combining disinfecting and air freshening properties. Bactericide destroys odour producing bacteria, effectively eliminating malodours at source. Pleasant perfume freshens all footwear. Rapid evaporation for quick drying.


Product Uses

A general all round disinfecting spray for all kinds of footwear and head gear.

Directions

Shake can well before use. Use in a well ventilated area. Hold can upright, 15 to 20cm from object to be sprayed. Two quick spray actions will disinfect/reodourise.

iN Insight Supported



iN Insight is Selden's interactive product selection and training system. Enables the user to create full COSHH training kits, wallcharts, task cards and more. visit <http://www.selden.co.uk/insight>


iN Insight recommended product uses

Special - shoe and helmet deodourising and disinfection

typical dilution n/a

Product Hazards and PPE Requirements

Danger



Contains : Isopropyl alcohol

Risk Phrases

Extremely flammable aerosol. Causes serious eye irritation. May cause drowsiness or dizziness. Pressurised container: May burst if heated.

Safety Phrases

Keep out of reach of children. Keep away from heat, sparks, open flames, hot surfaces. No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Wash hands thoroughly after handling. Use only outdoors or in a well-ventilated area. Wear eye protection, protective gloves. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention. Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122°F.

Technical Data

Composition	Perfume, aliphatic solvent and a bactericide.
Appearance	Clear spray
Colour	Colourless
Fragrance	Magnolia
Stability	Two years minimum
Statutory Conditions	All biocides/disinfectant/preservatives contained within Selden products fully comply with the EU Biocidal product Directive 98/8/EC, ensuring a high level of protection for humans, animals and the environment.
Storage	Pressurised container. Store out of direct sunlight. Temperature must not exceed 50°C

Aerosol Information

Propellant	Hydrocarbon
Pressure	56 psi
Spray Rate	0.8

Environmental Profile

Biodegradability

Selden Environmental Charter

- We set ourselves industry leading standards.
- Selden minimises wastage, packaging and transportation.
- If it can be recycled, it will be recycled.
- Our chemicals policy exceeds regulatory requirements.
- We don't expect other people to clean up after us.
- Conserving energy, preserving resources.
- By being innovative, we strive to do better.
- We like to work in partnership with our clients.


Visit our website for more information.

External Accreditations

- 9001 - Quality System
- 14001 - Environmental System
- 18001 - Health & Safety System
- IPPC Certified Manufacturer


Sustainability

Product conforms with the DEFRA endorsed Sustainable Cleaning guidance



COSHH+ Supported

Selden's bespoke COSHH awareness and product training tool. Users specify the products in use and instantly generate a full training pack to enable quick and effective staff training.



www.flagship-mcp.com

Flagship products are those products that are included in Selden Multi-language Cleaning Programme. Flagship products have induction kits, best practise guidance, MSDS, wallcharts and usage guides available in the following languages

- english, french, spanish, portuguese, polish, german, dutch, russian, romanian, estonian, czech, croatian.



UKAS
accredited testing
laboratory No. 4204



SELDEN
formulating
testing
manufacturing
to
the highest
standards

Selden Research Limited

Staden Business Park, Staden Lane, Buxton Derbyshire. SK17 9RZ

Tel : 01298 26226 | Fax : 01298 26540 | Email : info@selden.co.uk | web : www.selden.co.uk

