



Part Number: 8744

Audio/Control/Instrumentation, (9 pr) 22 AWG Solid TC, PVC/PVC, CMG

Product Description

Nine 22 AWG pairs solid tinned copper conductors, twisted pairs, PVC insulation, PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
22	Solid	TC - Tinned Copper	9

Conductor Count:	18
Total Number of Pairs:	9
AWG Size:	22

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.01 in

Color Chart

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown
7	Black & Orange
8	Red & White
9	Red & Green

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.35 in	0.035 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
16.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
30 pF/ft

Current

Max. Recommended Current [A]

1.40 Amps per conductor @ 20°C

Voltage

UL Description	UL Voltage Rating
CMG	300V RMS CMG
UL AWM Style 2576	150 V RMS UL AWM Style 2576

Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2576)
Operating Temp Range:	-20°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	71 lbs/1000ft
Max Recommended Pulling Tension:	140 lbs
Min Bend Radius/Minor Axis:	3.5 in

Standards

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
UL AWM Style:	UL Style 2576 (150 V 80°C)

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4

Part Number

Plenum (Y/N):	No
---------------	----

Variants

Item #	Color	Footnote
8744 0601000	CHROME	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.