

75 Watts

- Ultra Slim Design - 32 mm
- 150% Peak Load for 3 seconds
- Ambient Operation from -25 °C to +70 °C
- Full Load at 60 °C
- High Efficiency - Up to 91%
- Volt-Free Contact for DC OK
- Selectable Parallel Operation
- 85 to 264 VAC Operation
- 3 Year Warranty



Dimensions:

DSR75:

1.26 x 4.88 x 4.69" (32.0 x 124.0 x 119.0 mm)


Models & Ratings

| Output Voltage | Output Power | Output Voltage Trim ⁽³⁾ | Output Current | Peak Current ⁽²⁾ | Typical Efficiency ⁽¹⁾ | Model Number |
|----------------|--------------|------------------------------------|----------------|-----------------------------|-----------------------------------|--------------|
| 12 V | 75 W | 12.0-14.0 V | 6.3 A | 9.45 A | 88% | DSR75PS12 |
| 24 V | 75 W | 24.0-28.0 V | 3.2 A | 4.80 A | 91% | DSR75PS24 |
| 48 V | 75 W | 48.0-56.0 V | 1.6 A | 2.40 A | 91% | DSR75PS48 |

Notes

1. Typical efficiency at 230 VAC and full load.
2. Peak current is for a maximum of 3 s, see Application Notes. Average power is not to exceed nominal output power.
3. Output current should be limited so that nominal output power is not exceeded.

Mechanical Details



| Pin Connector | | |
|---------------|-----|-------------|
| Conn | Pin | Designation |
| AC I/P | 1 | L |
| | 2 | N |
| | 3 | Ground |
| DC O/P | 1 | DC OK |
| | 2 | DC OK |
| | 3 | -Vout |
| | 4 | +Vout |

Notes

1. All dimensions in inches (mm)
2. Weight: 1.06 lbs (480g)
3. Tolerance: ±0.02 in (±0.5 mm)

Input

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|---------------------------|--------------------------------------|---------|---------|-------|---|
| Input Voltage - Operating | 85 | | 264 | VAC | |
| Input Frequency | 47 | 50/60 | 63 | Hz | |
| Power Factor | | 0.95 | | | At 230 VAC. Conforms to EN61000-3-2 Class A |
| Input Current - Full Load | | 0.8/0.4 | | A | 115/230 VAC |
| Inrush Current | | | 30/60 | A | At 115/230 VAC. Cold Start, 25 °C |
| Earth Leakage Current | | | 1.0 | mA | At 264 VAC, 60 Hz |
| Input Protection | T5.0 A / 250 V internal in-line fuse | | | | |

Output

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|---------------------------|---------|---------|-------------|----------|---|
| Output Voltage - V1 | 12 | | 48 | VDC | See Models and Ratings table |
| Initial Set Accuracy | | | ±1 | % | At 100% load |
| Output Voltage Adjustment | | | | % | See Models and Ratings table |
| Minimum Load | 0 | | | A | No minimum load required |
| Start Up Delay | | | 500 | ms | At 100 VAC |
| Hold Up Time | 20 | | | ms | At full load |
| Line Regulation | | | ±0.5 | % | |
| Load Regulation | | | ±1 | % | |
| Transient Response - V1 | | | 5 | % | Recovery within 1% in less than 200 µs for a 50% step load change at 0.2 A/µs |
| Ripple & Noise | | | 100/120/240 | mV pk-pk | 12 V/24 V/48 V models. Measured at 20 MHz bandwidth 0-70°C |
| | | | 200/240/240 | | 12 V/24 V/48 V models. Measured at 20 MHz bandwidth -25-0°C |
| Overvoltage Protection | 15 | | 18 | V | 12 V model |
| | 29 | | 33 | V | 24 V model |
| | 58 | | 65 | V | 48 V model |
| Overload Protection | 110 | | 150 | % | Trip & restart. See application note. |
| Short Circuit Protection | | | | | Trip & restart (hiccup mode) for 5 cycles then latch. Recycle AC to reset. |
| Thermal Protection | | 100 ±5 | | °C | Measured internally auto recovery |
| Temperature Coefficient | | | 0.03 | %/°C | |

General

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|---|---|------------|---------|--------|----------------------------|
| Efficiency | | 91 | | % | See Models & Ratings table |
| Isolation: Input to Output Input to Ground Output to Ground | 3000 | | | VAC | |
| | 2500 | | | VAC | |
| | 500 | | | VAC | |
| Switching Frequency | | 65 | | kHz | PFC, Fixed |
| | 60 | | 300 | kHz | Main converter, Variable |
| DC OK Signal | Volt free contacts rated at 60 VDC/0.3 A, 30 VDC/1.0 A or 30 VAC/0.3 A (resistive load) | | | | |
| Output LED | Green LED to indicate output on. | | | | |
| Mean Time Between Failure | 300 | | | kHrs | MIL-HDBK-217F, +25 °C GB |
| Weight | | 1.06 (480) | | lb (g) | |

Environmental

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|-----------------------|---------|---------|---------|-------|---|
| Operating Temperature | -25 | | +70 | °C | See derating curve in Application Notes |
| Storage Temperature | -40 | | +85 | °C | |
| Cooling | | | | | Natural convection |
| Operating Humidity | 20 | | 95 | %RH | Non-condensing |
| Operating Altitude | | | 5000 | m | |
| Shock | | 4 | | g | IEC68-2-27, 22 ms half sine, 3 times in each of 6 axes |
| Vibration | | 2 | | g | IEC68-2-6, 10-500 Hz, 10 mins/sweep. 60 mins for each of 3 axes |

EMC: Emissions

| Phenomenon | Standard | Test Level | Criteria | Notes & Conditions |
|----------------------|-------------|------------|----------|--------------------|
| Conducted | EN55032 | Class B | | |
| Radiated | EN55032 | Class B | | |
| Harmonic Current | EN61000-3-2 | Class A | | |
| Voltage Fluctuations | EN61000-3-3 | | | |


EMC: Immunity

| Phenomenon | Standard | Test Level | Criteria | Notes & Conditions |
|------------------------|-------------|----------------------|----------|--------------------|
| ESD Immunity | EN61000-4-2 | 6 kV | A | Contact |
| | | 8 kV | | Air Discharge |
| Radiated Immunity | EN61000-4-3 | 10 V/m | A | |
| EFT/Burst | EN61000-4-4 | 3 | A | |
| Surges | EN61000-4-5 | Installation class 3 | A | |
| Conducted | EN61000-4-6 | 10 V | A | |
| Magnetic Fields | EN61000-4-8 | 4 | A | |
| Dips and Interruptions | EN55024 | Dip: 30%, 10 ms | A | |
| | | Dip: 60%, 100 ms | A/B | High Line/Low Line |
| | | Dip: 100%, 5000 ms | B | |

Safety Approvals

| Safety Agency | Safety Standard | Notes & Conditions |
|---------------|-----------------|---|
| UL | UL508/UL60950 | Industrial Control Equipment/Information Technology |
| TUV | EN60950-1 | Information Technology |
| CB | IEC60950-1 | Information Technology |

Mechanical Details



| Pin Connector | | |
|---------------|-----|-------------|
| Conn | Pin | Designation |
| AC I/P | 1 | L |
| | 2 | N |
| | 3 | Ground |
| DC O/P | 1 | DC OK |
| | 2 | DC OK |
| | 3 | -Vout |
| | 4 | +Vout |


Notes

- All dimensions in inches (mm)
- Weight: 1.06 lbs (480 g)
- Tolerance: ± 0.02 in (± 0.5 mm)

Application Notes

Derating Curves


DSR75PS12




Application Notes

Derating Curves

DSR75PS24



DSR75PS48



DC OK



Open = Output fail, if voltage drops below 80% of nominal
 Closed = Output good

Contact Rating: 0.3 A at 60 VDC, 1.0 A at 30 VDC, 0.5 A at 30 VAC.
 500 VDC isolation to output.

Peak Load and Overload

A peak load can be used for a certain period after which the output goes into overload mode. Overload operation is trip and restart. The peak load duration depends on the value of the load, e.g. a peak load of 150% can be taken for approximately 3s. After this time the output will turn off for approximately 7s before turning back on.

If the load has reduced to 100% or less than normal operation is resumed. If the load remains at 150% then the output is maintained for a further 3s before turning off for 7s. See example plot below.



If the peak load is less than 150%, the duration of the peak can be longer than 3s before the output turns off, for example, a peak load of 130% could typically be taken for up to 13s and a peak load of 140% could typically be taken for up to 5s. The off duration is always approximately 7s.

Average power is not to exceed nominal output power.