

Shrink sleeve - MM-WMS-2 9,5 (EX16)R C1 WH/BK - 0803930


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 4.8 - 9.5 mm, can be marked with THERMOFOX

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 212104
GTIN	4055626212104
Weight per Piece (excluding packing)	61.200 g
Custom tariff number	39173200
Country of origin	China

Technical data

Dimensions

Length (b)	1.8 m
Width (a)	16 mm
Cable diameter	4.8 mm ... 9.5 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

General

Color	white
Base element material	polyolefine
Type	Shrink sleeve
Components	free from silicone, halogen, and cadmium
Material	Polyolefine
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	slide on

Shrink sleeve - MM-WMS-2 9,5 (EX16)R C1 WH/BK - 0803930

Technical data

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400105
eCl@ss 9.0	27400401

ETIM

ETIM 3.0	EC001530
ETIM 4.0	EC000217
ETIM 5.0	EC000217
ETIM 6.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504