

HyperLink Wireless brand 2.4 GHz 8 dBi Wireless LAN Flat Patch Antenna

Model: HG2409P

Applications and Features

- Applications:**
- 2.4 GHz ISM Band
 - IEEE 802.11b and 802.11g Wireless LAN
 - Bluetooth®
 - Public Wireless Hotspot
 - WiFi
- Features:**
- Superior performance
 - Compact size, 4.5" Square
 - Durable UV-stable, UL flame rated radome
 - Low loss solid brass element
 - DC Short lightning protecting
 - 12 inch coax lead
 - Can be installed for either vertical or horizontal polarization
 - Optional mounting brackets available



Description

This very compact flat patch Wi-Fi antenna provides 8 dBi gain with very broad coverage. It is suitable for both indoor and outdoor applications in the 2.4GHz ISM band, including IEEE 802.11b and 802.11g, Bluetooth® and for public wireless hotspot applications. This WiFi antenna is lightweight and features an aesthetic UV-stable, UL flame rated white plastic radome which can also be painted to match the room or building structure. The HG2409P can be installed for horizontal or vertical polarization. It can be wall or ceiling mounted, as well as mast-mounted using U-bolts.

Specifications


Electrical Specifications

Frequency	2400-2500 MHz
Gain	8 dBi
Horizontal Beam Width	75 degrees
Vertical Beam Width	65 degrees
Impedance	50 Ohm
VSWR	< 1.5:1 avg.
Lightning Protection	DC Short

Mechanical Specifications




Weight	0.4 lbs. (.18 Kg)
Dimensions	4.5 x 4.5 x .9 inches 114 x 114 x 23 mm
Radome Material	UV-inhibited Polymer
Flame Rating	UL 94HB
Operating Temperature	-40° C to to 85° C (-40° F to 185° F)
Mounting	Four ¼ in. (6.3 mm) Holes
Polarization	Horizontal or Vertical
Wind Survival	>150 MPH (241 KPH)







Antenna Gain Patterns



Mounting Options

Hyperlink's patch antennas offer several unique mounting options. They can be mounted flat against a wall, or to a mast using a pair of 2 inch U-bolts. The antennas also accept most tilt-and-swivel security camera brackets equipped with standard 1/4-20 threads.

	Description	Part Number
	Small Metal Tilt-and-Swivel Mounting Bracket for indoor wall mounting. Includes wall-mounting hardware.	HGX-PMT02
	Medium Plastic Tilt-and-Swivel Mounting Bracket for indoor wall mounting. Includes wall-mounting hardware.	HGX-PMT03
	Large Metal Tilt-and-Swivel Mounting Bracket for indoor and outdoor wall or mast mounting. Includes wall-mounting hardware. Can be mast-mounted using U-Bolt Kit (sold separately).	HGX-PMT04

	<p>Universal Antenna Mount powder coated galvanized steel "DSS-style" arm for outdoor wall mounting. Requires a pair of 2 inch U-bolts (sold separately).</p>	<p>HGX-UMOUNT</p>
	<p>Stationary Mounting Kit for mounting to 1-1/4" to 2" dia. masts. Includes U-Bolts, nuts and mast clamp.</p>	<p>HGX-PMT07</p>
	<p>60 Degree Tilt-and-Swivel Mounting Kit for mounting to 1-1/4" to 2" dia. masts. Mounting hardware included.</p>	<p>HGX-PMT06</p>
	<p>Ceiling/Wall Universal Antenna Mount can be used with HyperLink's 4.5" sq and 8.5" sq. patch antennas as well as N-Type bulkhead and TNC/BNC bulkhead omni directional antennas. Includes ceiling/wall mounting hardware.</p>	<p>HGX-UMOUNT02</p>
	<p>Universal Corner Mounting Bracket: This bracket is designed to mount to an outside corner of a structure. It can be used with HyperLink's 4.5" and 8.5" sq. patch antennas, radome enclosed Yagi antennas, the HGX-PMT02 tilt & swivel bracket and can also accommodate the SC2402N and SC5802N 2-Way signal splitters as well as HyperAmp outdoor amplifiers.</p>	<p>HGX-UMOUNT03</p>
	<p>Window Mounting Kit Includes suction cups and mounting hardware.</p>	<p>HGX-PMT08</p>