R&S®FPC1500 Spectrum Analyzer with the Value of Three

Unexpected performance in entry class



The perfect choice for	
R&D and service labs	Test automation
Professional hobbyists	Education and training

Key specification	ns
Frequency range	5 kHz to 1 GHz with upgrades up to 3 GHz
Max. input power	Up to +30 dBm
Low noise floor	Down to -165 dBm (typ. with preamplifier)
Connectivity	LAN, USB, Wi-Fi (optional)
Measurement options	modulation analysis, receiver mode, advanced measurements
Tracking Generator	5 kHz to 1/2/3 Ghz

Your benefit	Features
Value of three	R&S*FPC1500 combines the value of a spectrum analyzer, a vector network analyzer and a signal generator
More resolution for better measurements	Lowest noise floor in its class, down to –165 dBm (typ. with preamplifier), Resolution bandwidth down to 1 Hz, 10.1" WXGA display
Investment protection	All upgrades available via keycode, no additional calibration required

Value of three R&S*FPC1500 combines three instruments in one:

■ Spectrum analyzer

The R&S°FPC1500 base instrument has a frequency range from 5 kHz to 1 Ghz with keycode options to unlock up to 3 GHz and other features. Engineered in Germany, it provides the best dynamic range in its class. In combination with RBW settings down to 1 Hz, it resolves the finest details, which are displayed on the high-resolution 10.1" WXGA display. Wired or wireless remote control options are available free of charge.

Network analyzer


The R&S°FPC1500 features an internal VSWR bridge that makes purchasing and mounting/ dismounting an external bridge unnecessary. S11 reflection measurements are supported, including Smith chart and DTF features.


Signal generator


The R&S°FPC1500 not only features standard tracking generator measurements with frequency offset functionality, its signal source is independent to enable signal generator functionality. A CW signal can be set within the frequency range, or in a coupled mode to follow the center frequency setting of the spectrum analyzer mode.

 For more information, see www.rohde-schwarz.com/product/fpc1500









Ordering information

Model configuration information		
Base unit	Description	
F&S®FPC1500	R&S°FPC1500 spectrum analyzer, 5 kHz to 1 GHz	
Option	Description	
R&S®FPC-B2	Spectrum analyzer frequency upgrade, 1 GHz to 2 GHz	
R&S®FPC-B3	Spectrum analyzer frequency upgrade, 2 GHz to 3 GHz	
R&S®FPC-B22	Spectrum analyzer preamplifier	
R&S®FPC-B200	Wi-Fi connection support	
R&S®FPC-K7	Modulation analysis	
R&S®FPC-K42	Vector network analysis	
R&S®FPC-K43	Receiver mode	
R&S®FPC-K55	Advanced measurements	
Accessories	Name	
R&S®ZZA-FPC1	19" rackmount kit	
R&S®HZ-15	Near-field probes, 30 MHz to 3 GHz (set of 5 probes)	
R&S®HZ-16	Amplifier, 100 kHz to 3 GHz	
R&S®HZ-17	Near-field probes, 30 MHz to 3 GHz (set of 2 probes)	
R&S®RTB-Z3	Carrying case	

Rohde & Schwarz Representative

Rohde & Schwarz GmbH & Co. KG | Europe, Africa, Middle East +49 89 4129 12345 | North America 1 888 TEST RSA (1 888 837 87 72)

Latin America +1 410 910 79 88 | Asia Pacific +65 65 13 04 88 | China +86 800 810 82 28 / +86 400 650 58 96

www.rohde-schwarz.com | customersupport@rohde-schwarz.com

R&S® is a registered trademark of Rohde & Schwarz GmbH & Co. KG | PD 5215.7345.32 | Version 01.00 | March 2018 (ss)
Trade names are trademarks of the owners | R&S®FPC1500 Spectrum Analyzer | Data without tolerance limits is not binding
Subject to change | © 2018 Rohde & Schwarz GmbH & Co. KG | 81671 Munich, Germany