



DCG414N

54V XR Li-Ion Grinder

Selling Proposition

- 54V Brushless motor enables improved performance in demanding applications
- Electronic Brake stops the wheel quickly when the trigger is disengaged
- Electronic Clutch reduces the kickback reaction in the event of a pinch or stall
- Rubber overmold provides enhanced grip and comfort
- Recessed spindle lock design allows max depth of cut and greater protection to button when using in confined spaces
- Two position side handle offers greater comfort and control

Standard Equipment

- 2 position side handle
- Keyless protective guard
- Blade wrench
- Battery and charger sold separately

Warranty Specifications

- 3 year limited warranty

Specifications	
Power Input	1 Watts
No Load Speed	7000 rpm
Max. Disc Diameter	125 mm
Spindle Thread	M14
Weight	2.2 kg
Length	400 mm
Height	125 mm
Hand/Arm Vibration - Grinding	5.9 m/s ²