



## DEWALT 54V XR FLEXVOLT Circular Saw- Bare Unit (Battery Not Included)

DCS575N-XJ



- 54V XR FLEXVOLT Lithium-ion technology offers unrivalled cordless performance and power
- Ideal for ripping, cross-cutting and bevelling circular saw for wood and other construction materials
- High torque motor provides enhanced power and durability when cutting job site and joinery materials
- Quick variable adjustment bevel setting up to 57°
- Integrated LED light and Dust Blower for improved cut line visibility
- Ergonomic over mould touch points for improved comfort
- Cutting depth of up to 67 mm

### Description:

The DEWALT 54V XR FLEXVOLT 190mm Circular Saw is part of the XR FLEXVOLT Lithium-ion platform offering unrivalled enhanced runtime and performance, heavy-duty construction applications can be completed without the need for mains power. The XR FLEXVOLT battery pack is not only interchangeable across the 54V power tools range, but is also backwards compatible with all existing DEWALT 18V XR tools, allowing professionals to be able to operate every tool they need on a single cordless system. It has been constructed with a high torque brushless motor which delivers high performance and power of up to 5800 rpm. The brushless motor offers incredible efficiency and increased power delivery, resulting in less wear and increased longevity of the tool. The gearbox and blade guard have been encased in robust aluminum for greater durability. With a cutting depth setting of up to 67mm, this saw is perfect for ripping, cross cutting and beveling of various types of wood and job site sheet materials.

### Supplied With:

- 1 x Precision 24 tooth saw blade
- 1 x Rip Fence
- 1 x Blade Spanner
- 1 x Dust Extraction Spout

<b>Specifications</b>	
Battery	XR FLEXVOLT Lithium-Ion
Voltage	54 V
Battery Capacity	6.0 Ah
No Load Speed	5800 rpm
Blade Diameter	190 mm
Blade Bore	30 mm
Max. Depth of Cut at 90°	67 mm
Max. Depth of Cut at 45°	49 mm
Length	355 mm
Height	245 mm
Weight	3.6 kg