

CDP5EB DRILL PRESS

Product Overview:

This general purpose, five speed bench drill is ideal for the hobby or DIY user.

With a 13mm capacity chuck, compact dimensions and a whole host of other useful features, the CDP5EB is ideally suited for the home workshop. It also has a depth gauge and a height adjustable tilting table with slots to clamp your work piece.. For safety there's a clear Perspex chuck guard and a No Voltage Release switch, so it can't start unexpectedly should mains power fail temporarily (allowing insurance company approval for use in educational establishments) and it comes fitted with a 13amp plug. A front mounted reference chart has an accurate depth measurement scale which also shows the 5 drilling speeds available.



Technical Specifications:

- Chuck capacity 13mm (Spindle taper B16)
- 5 Speeds from 620 2620 RPM to suit wood, metal & plastic.
- 350 Watt, 230v / 1 phase electric motor (Totally Enclosed Fan Cooled)
- Safety features include electrical cut-out on belt guard, combined NVR/stop start switch & clear perspex chuck guard.
- Also has dry type tilting work table 160 x 160mm, depth gauge, user reference chart & fitted BS plug.
- Dimensions chuck to column 104mm (horizontal) & chuck to table 167mm (vertical)
- Dimensions chuck to column 104mm (horizontal) & chuck to table 167mm (vertical)