



## AERO DUSTER 100 INSTANT CLEANING WITHOUT SOLVENTS



**AERO DUSTER 100** is a liquefied gas which provides a dry, powerful blast for easy removal of dust and other loose contamination.

The product has been formulated without the use of any CFC's, HCFC's or HFC's. Low GWP of just 6, utilises the new HFO 1234ze.

### APPLICATIONS

Suitable for instant cleaning of inaccessible areas or where the use of solvents is not desirable. Can be used safely and efficiently on:

- Televisions
- Video and Audio Equipment
- Computers
- Cameras
- Business Equipment
- Tape Heads
- Clocks and Watches

The product should be held in a fairly upright position and sprayed directly onto the part to be treated. The extension tube helps to reach remote areas and components

### TECHNICAL DATA

Appearance	:	Gas at room temperature
Odour	:	Slight ethereal odour
SG @ 25°C	:	1.18
Pressure @ 25°C	:	4.9 Bar
Discharge Rate	:	0.5 g/sec
Solubility	:	Not Applicable
Flammability	:	Non-flammable (according to directive 2008/47/EC)*
Flashpoint	:	Not applicable in sealed aerosol
Packaging	:	200ml aerosol
GWP	:	6
Propellant	:	HFO 1234ze

## **STORAGE**

The product may be stored at normal ambient temperatures and has a shelf life of not less than 72 months with correct storage. Aerosols should always be stored below 50°C, away from direct heat and naked flame.

## **HEALTH AND SAFETY**

Health and Safety sheet available separately.

### **\* Remark regarding flammability:**

Although classified as nonflammable by GHS, DOT, IATA and IMDG and as measured by ASTM E-681 and ISO 10156, Solstice® Propellant (HFO-1234ze) can exhibit vapor flame limits at elevated temperatures. Solstice® Propellant has a very narrow flammable range (LFL-UFL) of 8.0-8.5 volume percent in air at one atmosphere under the following conditions:

- Temperature is 86°F (30°C), (and)
- Relative Humidity ≥50%, (and)
- High energy ignition source or open flame is present

Accordingly, CRC recommends that for use on energized electrical equipment the ambient temperature should be below 28C.

## **MISREPRESENTATION ACT 1967**

## **TRADE DESCRIPTIONS ACT 1968**

The information given in this publication is based on our experience and reports from customers. There are many factors outside our control and knowledge which affect the use and performance of our products and for which reason no warranty is given, express or implied. Users should make their own tests to determine the applicability of such information or the suitability of any products for their own particular purposes. Statements concerning the use of the products described herein are not to be construed as recommending the infringement of any patent and no liability for infringement arising out of any such use is to be assumed.

CRC Industries UK Limited, Wylds Road, Bridgwater, Somerset, TA6 4DD

Tel: +44 (0) 1278 727200

Fax: +44 (0) 1278 425644

Web: [www.ambersil.com](http://www.ambersil.com)

E-mail: [sales.uk@crcind.com](mailto:sales.uk@crcind.com)

Version 1

Updated :January 2018