


## SPE-150/WS - Loudspeaker



### Flush-mount full range speakers, 15 W

- Dual cone
- Slimline design with fixed metal grille



## Technical Data

|                         |   |
|-------------------------|---|
| Frequency range         | : 100-12,000 Hz                             |
| Resonant frequency (fs) | : -   |
| Power capability, 100 V | : -   |
| Power capability, 4 Ohm | : 30 W <sub>MAX</sub> , 15 W <sub>RMS</sub> |
| SPL (1 W/m)             | : 89 dB                                     |
| Type of speaker         | : 130                                       |
| Mounting cutout         | : Ø 120 mm                                  |
| Mounting depth          | : 34 mm                                     |
| Admiss. ambient temp.   | : 0-40 °C                                   |
| Dimensions              | : Ø 153 mm x 45 mm                          |
| Weight                  | : 500 g                                     |
| Other features          | : -   |