

EVC 500 Main Contactor

- Limiting continuous current 500A at 85°C (with 400mcm conductors)
- Hermetically sealed
- UL approved

Typical applications

- DC high voltage high current applications
- · Main contactors for hybrid, full battery electric vehicles and fuel-cell cars
- Battery charging systems



3D500_fbw5

Contact Data	
Contact arrangement	1 Form X (SPST NO DM)
Rated operating voltage	450VDC (450-900VDC) ¹⁾
Continuous carry current ²⁾	
85°C, load cable 214mm ² /400mcm	500A
Limiting short-time current	
85°C, load cable 107mm²/200mcm	500A / 7.5min
	1000A / 1min
	2000A / 15s
Make/break current at various voltages	see graph on page 3
Limiting break current, forward direction	
resistive load, 23°C, 450VDC	1 x 1560A
Load life	see graph on page 3
Initial contact voltage drop at 200A, 30s	<100mV
Operate / release time max.	
close (includes bounce)	20 ³⁾
bounce (after close only)	7
release (includes arcing) at 2000A	12
Mechanical life	>500,000 cycles

- 1) Suitable for voltages up to 450VDC with limited capability to 900VDC.
- Maximum allowed terminal temperatures are: 150°C continuous; 175°C for 2h; 200°C for 2min.
- 20ms (max.) at rated 12V. Consult TE Connectivity for operating time not done at rated voltage.

Coil Data⁴⁾

Econ	omized coil wit	th internal ecor	nomizer (valid	d from -40°	C to 85°C)
Coil	Operating	Inrush current	Max. inrush	Nominal	Nominal
code	voltage range	at 23°C	time	frequency	duty cycle
	VDC	Α	ms	kHz	%
Α	9 to 36	3.8	130	19.9	20

Un-economized coil for external economization5)

(Coil	Rated	Pull-in v	voltage	Drop-ou	ut voltage	Min. hold	Coil
C	code	voltage	min.	max.	max.	min.	current	resistance
		VDC	VDC	VDC	VDC	VDC	mA	Ω -5 %/+10%
	1	12	4.2	6.5	1.5	0.5	650 ⁶⁾	3.14

- 4) All data valid at 23°C coil temperature.
- 5) Un-economized coil must be economized by the customer to avoid overheating.
- 6) Must operate at 12V for 100ms before reducing to minimum holding current.

0-:1	Data	(continued	ä
COII	Data	ccommuec	1

Recommended PWM parameters for customer supplied economizer circuit (valid from -40°C to 85°C)

	Operating	Coil Current (min.	Duty	Max. inrush				
Frequency	voltage range	recommended	cycle	time				
kHz	VDC	RMS) mA	%	ms				
16 to 20	8.5 to 16	650	20 to 30	200				

Insulation Data	
Initial dielectric strength ⁷⁾	
between open contacts	2920VDC/leakage <1mA
between contact and coil	2920VDC/leakage <1mA
max. altitude	5000m
Inculation registered at EOOV/DC7)	

 $\begin{array}{ll} \text{Insulation resistance at 500VDC}^{7)} \\ \text{between open contacts} & >1 \text{ } \text{G}\Omega \\ \text{between contact and coil} & >1 \text{ } \text{G}\Omega \end{array}$

7) Meets dielectric strength and IR requirements according to ISO 6469-3, conformity to IEC60664-1 in preparation.

Other Data	
Material data	
EU RoHS/ELV compliant	
Ambient temperature	-40°C to +85°C
Vibration resistance (functional)	
sine sweep/peak	80-2000Hz/20g
Shock resistance (functional)	
coil energized, peak	50g
Terminal type	stripped wires (coil) and screw (load)
Weight	approx. 430g (0.95lb)

Terminal Assignment

Forward load current direction






EVC 500 Main Contactor (Continued)


Dimensions

EVC 500 main contactor without coil economizer



Dimensions

EVC 500 main contactor with internal economizer






EVC 500 Main Contactor (Continued)

Contact performance


Estimated make and break power switching ratings (forward direction)



Notes:

- 1) Maximum of 300µH for resistive load. Consult TE Connectivity for inductive loads.
- Estimates based on extrapolated data. Consult TE Connectivity to confirm performance in application.
- 3) End of life when "Insulation Resistance" between terminals falls below 50 M Ω at 500VDC.
- 4) The maximum make current is 650A to avoid contact welding.
- 5) Curves for voltages above maximum rated voltage for information purpose only.
- 6) For reverse current switching capability, please contact TE Connectivity for details.


Contacts closed into capacitor precharge sequence at various time constants




Notes:

- 1) Because higher current cause more damage to contact surface, at least 95% precharge recommended.
- Inrush current dependent upon RC time constant and precharge timing sequence.

Estimated fuse guide for EVC 500 contactors (Reference only – not to be used for actual fuse sizing)



Coil inductance




Note:

Data points above were measured using Quadtech 1715 LCR Bridge set 10Ω range, 1V output, measured at 100Hz, 120Hz, 1kHz and 10kHz.



EVC 500 Main Contactor (Continued)



Production in Americas (only)

Product code	Contact arrang.	Coil	Circuit	Coil suppr.	Relay Type	Resistance	Part number
EVC 500-A1ANAM	SPDT-NO-DM	12VDC	No economizer	External >40V	450VDC	3.14Ω	2098372-1
EVC 500-AAANAM			Internal PWM	Internal			2098190-1

Production in Asia (only)

Product code	Contact arrang.	Coil	Circuit	Coil suppr.	Relay Type	Resistance	Part number
EVC 500-A1ANAM	SPDT-NO-DM	12VDC	No economizer	External >40V	450VDC	3.14Ω	2219561-1
EVC 500-AAANAM			Internal PWM	Internal			2299223-2