



# KEMET Part Number: ALF40G221EB400



ALF40, Aluminum Electrolytic, 105C, 220 uF, 20%, 400 VDC, -40/+105C



## General Information

<b>Supplier:</b>	KEMET
<b>Series:</b>	ALF40
<b>Dielectric:</b>	Aluminum Electrolytic
<b>Style:</b>	Press-Fit
<b>Description:</b>	Press-Fit, Aluminum Electrolytic
<b>RoHS:</b>	Yes
<b>Lead:</b>	5 Pin Press-Fit
<b>Notes:</b>	Dimensions Include Slewing
<b>Shelf Life:</b>	156 Weeks

## Dimensions

<b>D</b>	40mm +1mm
<b>L</b>	30mm +/-2mm
<b>S</b>	25mm +/-0.1mm
<b>LL</b>	5.5mm +/-1mm
<b>F</b>	1.486mm +/-0.076mm

## Packaging Specifications

<b>Weight:</b>	49 g
<b>Packaging:</b>	Bulk
<b>Packaging Quantity:</b>	72

## Specifications

<b>Capacitance:</b>	220 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	400 VDC, 440 VDC (Surge)
<b>Temperature Range:</b>	-40/+105C
<b>Rated Temperature:</b>	105C
<b>Life:</b>	9000 Hrs (Rated Voltage And Ripple Current At 105C), 14000 Hrs (Rated Voltage At 105C)
<b>Resistance:</b>	521 mOhms (100Hz 20C), 320 mOhms (10kHz 20C)
<b>Ripple Current:</b>	1.88 Amps (100Hz 105C), 4.36 Amps (10kHz 105C)
<b>Leakage Current:</b>	264 uA (5min 20C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2018 IntelliData.net