

IGBT BASED DC SOLID-STATE RELAY



SCI0251700



| | |
|------------------------------------|-----------|
| Control voltage range | 4.5-32VDC |
| Max transient peak voltage | 1700v |
| Advised max. DC Mains peak voltage | 820VDC |
| Max. Load Current (with heatsink) | 25ADC |


- ▶ Latest high voltage IGBT technology generation.
- ▶ New innovative isolated driver ensuring fast power transistor turn on and off therefore low power transient.
- ▶ Ultra low output leakage current
- ▶ Low control current consumption
- ▶ Triggered control input to avoid linear control risks
- ▶ Low conducted and radiated disturbances

| DC Mains voltage range | Load current range | Control input voltage range | In & case / Out Insulation | Connections | Dimensions (WxHxD) | Weight |
|---|--------------------------|-----------------------------|----------------------------|--------------------------------|-----------------------|--------|
| 820VDC Max Advised (Depends on protection clamping voltage) | 0 to 25A (with heatsink) | 4.5-32VDC | 4kV | M3 round tabs M5 round tabs | 44.5 x 58.2 x 27 (mm) | 100g |




Proud to serve you

CONTROL INPUT CHARACTERISTICS

| INPUT CIRCUIT | CHARACTERISTIC | LABEL | VALUE | INFO. | Fig. 4  | CONTROL CURRENT vs. CONTROL VOLTAGE | |
|---------------|------------------------------|----------|--------------------|---------------|--|-------------------------------------|--|
| | Nom. Control voltage | Ucnom | 12-24VDC | | | | |
| | Nom. Control current | Icnom | 35mAADC | | | | |
| | Control voltage range | Uc | 4.5 – 32VDC | typical=4.3V | | | |
| | Control current consumption | Ic | 25 – 42mAADC | See curve | | | |
| | Releasing control voltage | Ucoffmax | 1VDC | Typical= 3.5V | | | |
| | Max. reverse control voltage | -Ucmax | 32VDC | -Icmax <100µA | | | |
| | Input impedance | Rin | Current limitation | See curve | | | |

TIME CHARACTERISTICS

| TIME CHARACT. | CHARACTERISTIC | LABEL | VALUE |  | TIME CHARACTERISTICS | |
|---------------|-----------------------|-----------|-------|--|----------------------|--|
| | Turn on time | ton | 10µs | | | |
| | Turn on delay | tdon | 600µs | | | |
| | Turn off time | toff | 50µs | | | |
| | Turn off delay | tdoff | 100µs | | | |
| | Max. On-Off frequency | F(on-off) | 200Hz | | | |

POWER OUTPUT CHARACTERISTICS

| POWER CIRCUIT | CHARACTERISTIC | | LABEL | VALUE | INFO. |
|---------------|---|----------|-------------|--|---|
| | Mains voltage range | Ut | Ue | Min = VCEsat Max (Advised) = 820VDC | Depends on protection clamping voltage (D1) |
| | Non-repetitive peak voltage | Utp | | 1700V | |
| | Overvoltage protection | D1 | | Not integrated A voltage clamping mean must be connected across the terminals 1 & 2 (see fig 1 & 2) | Please consult us to select the right protective components |
| | Off-state max reverse voltage drop (internal diode) | -Ut | | 3.3V | @Ie=16A |
| | Maximum nominal currents | Ie max | Resistive | | See fig. 9 |
| | | | 50A | Please contact us | |
| | Max. non-repetitive peak current | Iepeak | 40A / 1ms | | @Tc=25°C |
| | Min. load current | Iemin | 5mA | | |
| | Max. leakage current | Ielk max | 1.5mA | | @Utp @Tjmax |
| | Max. on-state voltage | VCEsat | 3.3V | | @Ie=16A |
| | Typ. output capacitance | Cout | 90pF | | @Utp |
| | Junction/case thermal resistance | Rthjc | 1.25K/W | | |
| | Built-in heatsink thermal resistance vertically mounted | Rthra | 10K/W | | @ΔTra=75°C |
| | Heatsink thermal time constant | Tthra | 10 minutes | | @ΔTra=60°C |
| | Control inputs/power outputs insulation voltage | Uimp | 4kV | | |
| | Inputs/case insulation voltage | Uimp | 4kV | | |
| | Outputs/case insulation voltage | Uimp | 4kV | | |
| | Isolation resistance | Rio | 1GΩ | | |
| | Isolation capacitance | Cio | <8pF | | |
| | Maximum junction temperature | Tjmax | 175°C | | |
| | Storage ambient temperature | Tstg | -40->+100°C | | |
| | Operating ambient temperature | Tamb | -40->+90°C | | See fig. 9 |
| | Max. case temperature | Tc | 100°C | | |

OUTPUT SWITCH CHARACTERISTIC CURVES

Fig. 5

VOLTAGE DROP VS LOAD CURRENT




Fig. 6

REVERSE VOLTAGE DROP VS REVERSE CURRENT




Fig. 7

POWER ELEMENT TRANSIENT THERMAL IMPEDANCE vs. PULSE DURATION




Fig. 8

ON-STATE PEAK OVERLOAD CURRENT vs. PULSE DURATION





Fig. 9

POWER DISSIPATED AND LOAD CURRENT LIMIT VS TEMPERATURE

Permanent current
Ie (ARMS)Please refer to the installation notice for precautions about
mounting the device on a heatsink.Power dissipated
Pd (W)10K/W = No Heatsink / 1LD12020
2.1K/W = WF210000
0.55K/W = WF0500004K/W = 150x150x3mm aluminium sheet
1.2K/W = WF121000
0.3K/W = WF0311001.1K/W = WF131100
0.2K/W = No reference2.2K/W = WF262100 / WF151200
0.9K/W = WF115100
0.1K/W = No reference

0.75K/W = WF070000

GENERAL INFORMATION

| CONNEX- TIONS | Connections | | Power | Control | |
|------------------|---|--|--------------|----------------|--|
| | Screwdriver advised | | Philips™ NR2 | Philips™ NR1 | |
| | Min and max tightening torque | | 1.8 N.m | 0.8 N.m | |
| | Insulated crimp terminals (round tabs, eyelet type) | | M5 | M3 | |

| | | | | |
|-------|--------------------|--|--|--------------------|
| MISC. | Display | | Green LED (indicates relay has switched ON) | |
| | Housing | | UL94V0 | |
| | Mounting | | 2 screws (M4x12mm) | See mounting sheet |
| | Noise level | | No audible noise | |
| | Weight | | 100g | |

STANDARDS

| | | | | |
|---------|--|--|------------|--|
| GENERAL | Standards | | IEC60947-1 | |
| | Protection level | | IP00 | |
| | Protection against direct touch | | None | |
| | CE marking | | Yes | |
| | UL, cULUS | | Yes | |


| E.M.C. IMMUNITY | TYPE OF TEST | STANDARD | LEVEL | EFFECT |
|--------------------|-----------------------------------|-----------------|--------------|---------------|
| | E.S.D. (Electrostatic discharges) | EN61000-4-2 | Pending | ? |
| | Radiated electromagnetic fields | EN61000-4-3 | Pending | ? |
| | Fast transients bursts | EN61000-4-4 | Pending | No effect |
| | Electric chocks | EN61000-4-5 | Pending | ? |
| | Voltage drop | EN61000-4-11 | - | |

| | | | | |
|--------------------|-------------------------------------|-----------|---------|--|
| E.M.C. EMISSION | Radiated and conducted disturbances | NFEN55011 | Pending | |
| | | | | |


DIMENSIONS AND ACCESSORIES

Fig.
10

DIMENSIONS (mm)



ACCESSORIES

PROTECTIVE COVER
1K470000

Please consult our website for other accessory references
(Heatsinks, mounting adaptors, thermal grease...)