



Vishay

HALOGEN

FREE GREEN

Wet Tantalum Capacitors, Ultra High Capacitance, Tantalum-Case with Glass-to-Tantalum Hermetic Seal for -55 °C to +125 °C



PERFORMANCE CHARACTERISTICS

Refer to: Typical Performance Characteristics

Operating Temperature: -55 °C to +85 °C


(to +125 °C with voltage derating)

Capacitance Tolerance: ± 10 %, ± 20 % standard

DC Leakage Current (DCL Max.): at +25 °C and above: leakage current shall not exceed the values listed in the Standard Ratings table.

FEATURES


- · Enhanced performance, high reliability design
- Terminations: axial, standard tin / lead (SnPb), 100 % tin available **RoHS**³
- Model T18 tantalum-case electrolvtic capacitors provide all the advantages of Vishay's SuperTan® series devices, while offering improved reverse voltage and vibration capability



- Designed for the avionics and aerospace applications
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Note

This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details



Note

Packaging: the use of formed plastic trays for packing bulk components is standard

DIMENSIONS in inches [millimeters]						
0.0253 ± 0.002 [0.64 ± 0.05] dia. (no. 22 AWG) tinned nickel leads solderable and weldable						
CASE	CODE ST	D	L ₁	L ₂	E	WEIGHT (g) (max.)
A	T1	0.188 ± 0.016 [4.78 ± 0.41]	0.453 + 0.031 / - 0.016 [11.51 + 0.79 / - 0.41]	(max.) 0.734 [18.64]	1.500 ± 0.250 [38.10 ± 6.35]	2.6
В	T2	0.281 ± 0.016 [7.14 ± 0.41]	0.641 + 0.031 / - 0.016 [16.28 + 0.79 / - 0.41]	0.922 [23.42]	2.250 ± 0.250 [57.15 ± 6.35]	6.2
С	Т3	0.375 ± 0.016 [9.52 ± 0.41]	0.766 + 0.031 / - 0.016 [19.46 + 0.79 / - 0.41]	1.047 [26.59]	2.250 ± 0.250 [57.15 ± 6.35]	11.6
D	T4	0.375 ± 0.016 [9.52 ± 0.41]	1.062 + 0.031 / - 0.016 [26.97 + 0.79 / - 0.41]	1.343 [34.11]	2.250 ± 0.250 [57.15 ± 6.35]	17.7

For insulated parts, add 0.015" [0.38 mm] to the diameter. The insulation shall lap over the ends of the capacitor body

www.vishay.com

STANDARD RATINGS

STANDAND NATINGS										
CAPACITANCE AT +25 °C	CASE	PART NUMBER	MAX. ESR AT +25 °C	MAX. IMP. AT -55 °C	MAX. DCL (µA) AT		MAX. CAPACITANCE CHANGE AT (%)		AC RIPPLE +85 °C	
120 Hz CODE (μF)			120 Hz (Ω)	120 Hz (Ω)	+25 °C	+85 °C / +125 °C	-55 °C	+85 °C	+125 °C	40 kHz (mA _{RMS})
	50 V _{DC} AT 85 °C, 30 V _{DC} AT 125 °C									
110	А	T18A117(1)050(2)(3)(4)(5)	1.80	40.00	2	7.5	-40	14	16	1500
	60 V _{DC} AT 85 °C, 40 V _{DC} AT 125 °C									
1000	D	T18D108(1)060(2)(3)(4)(5)	0.50	5.50	20	120	-60	10	15	3500
75 V _{DC} AT 85 °C, 50 V _{DC} AT 125 °C										
180	В	T18B187(1)075(2)(3)(4)(5)	1.50	30.00	5	25	-35	15	20	2000
750	D	T18D757(1)075(2)(3)(4)(5)	0.50	6.50	20	120	-45	12	15	3500
940	D	T18D947(1)075(2)(3)(4)(5)	0.50	8.00	20	200	-60	12	20	3500
1000	D	T18D108(1)075(2)(3)(4)S	0.50	8.00	20	200	-60	12	20	3500
1000	D	T18D108(1)075(2)(3)(4)L	0.35	8.00	20	200	-60	12	20	3500
1200	D ⁽¹⁾	T18D128(1)075(2)(3)(4)(5)	0.80	8.00	25	250	-70	16	30	3500
100 V _{DC} AT 85 °C, 65 V _{DC} AT 125 °C										
22	А	T18A226(1)100(2)(3)(4)(5)	3.00	100.00	1	5	-15	6	12	1200
86	В	T18B866(1)100(2)(3)(4)(5)	1.60	30.00	2	20	-20	6	12	2000
220	С	T18C227(1)100(2)(3)(4)(5)	1.40	18.00	5	25	-55	10	15	2500
400	D	T18D407(1)100(2)(3)(4)(5)	0.70	10.00	15	120	-50	8	15	3500
470	D	T18D477(1)100(2)(3)(4)(5)	0.70	10.00	25	250	-50	10	25	3500

Notes

.

Part number definitions:

(1) Capacitance tolerance: K, M

(2) Termination / packaging: C = 100 % tin, bulk; E = standard, tin / lead, bulk (3) Reliability level: Z = standard (non-ER / 500 g / 500 g / 27.78 g), H = high (non-ER / 500 g / 80 g / 53.79 g)

(4) Insulating sleeve: S = sleeved; U = unsleeved

(5) ESR: S =standard; L =low

⁽¹⁾ Rating in development, contact factory for availability

TYPICAL PERFORMANCE CHARACTERISTICS OF T18 CAPACITORS

ELECTRICAL CHARACTERISTICS					
ITEM	PERFORMANCE CHARACTERISTICS				
Operating temperature range	-55 °C to +85 °C (to +125 °C with voltage derating)				
Capacitor tolerance	± 20 %, ± 10 % at 120 Hz, at +25 °C				
Capacitor change by temperature	Limit per Standard Ratings table				
ESR	Limit per Standard Ratings table, at +25 °C, 120 Hz				
Impedance	Limit per Standard Ratings table, at -55 °C, 120 Hz				
DCL (leakage current)	Limit per Standard Ratings table				
AC ripple current	Limit per Standard Ratings table, at +85 °C and 40 kHz				
Reverse voltage	Reverse voltage shall be in accordance with MIL-PRF-39006, paragraphs 3.23 and 4.8.19, except DC potential will be maximum of 1.5 V.				
Surge voltage	Surge voltage shall be in accordance with MIL-PRF-39006. The DC rated surge voltage is the maximum voltage to which the capacitors can be subjected under any conditions including transients and peak ripple at the highest line voltage. The DC surge voltage is 115 % of rated DC voltage. After the test, the capacitors shall meet the following requirements: a) DC leakage shall not exceed the specified value in catalog b) Capacitance shall be within +5 %, -20 % of initial value				

Revision: 13-Mar-18



Vishay

PERFORMANCE CHARACTERISTICS			
ITEM	PERFORMANCE CHARACTERISTICS		
Life testing	Capacitors shall be capable of withstanding a 2000 h life test at a temperature +85 °C at rated voltage, or a 2000 h life test at 125 °C test at derated voltage. After the test, the capacitors shall meet the following requirements: a) DC leakage at 85 °C and 125 °C shall not exceed 125 % of the specified value b) DC leakage at 25 °C shall not exceed the specified value c) Capacitance shall be within + 10 %, - 20 % of initial value		

ENVIRONMENTAL CHARACTERISTICS				
ITEM	CONDITION	COMMENTS		
Seal	MIL-PRF-39006	When the capacitors are tested as specified in MIL-PRF-39006, there shall be no evidence of leakage.		
Moisture resistance	MIL-PRF-39006	Moisture resistance shall be in accordance with MIL-PRF-39006. Number of cycles: 10 continuous cycles		
Barometric pressure (reduced)	MIL-STD-202, method 105, condition E	Altitude 150 000 feet		

MECHANICAL CHARACTERISTICS				
ITEM	CONDITION	COMMENTS		
Shock (specified pulse)MIL-STD-202, method 213, codes Z and H = test condition D (500 g)		The capacitors shall meet the requirements of MIL-PRF-39006		
Vibration, high frequencyMIL-STD-202, method 204, code Z = test condition E (50 g peak) code H = test condition H (80 g peak)		The capacitors shall meet the requirements of MIL-PRF-39006.		
Random vibrationMIL-STD-202, method 214, code Z and H = test condition II-K (53.79 g RMS)		The capacitors shall meet the requirements of MIL-PRF-39006.		
Thermal shock MIL-STD-202, method 107, condition A		Thermal shock shall be in accordance with MIL-PRF-39006 when tested for 300 cycles.		
Solderability MIL-STD-202, method 208, ANSI/J-STD-002, test A		Solderability shall be in accordance with MIL-PRF-39006.		
Terminal strength	MIL-STD-202, method 211	Terminal strength shall be in accordance with MIL-PRF-39006.		
Resistance to solder heat	MIL-STD-202, method 210, condition C	The capacitors shall meet the requirements of MIL-PRF-39006.		
Terminals	MIL-STD-1276	Terminals shall be as specified in MIL-STD-1276. The length and diameter of the terminals shall be as specified in Dimensions table. All terminals shall be permanently secured internally and externally, as applicable. All external joints shall be welded.		
Marking MIL-STD-1285		Marking of capacitors conforms to method I of MIL-STD-1285 an include capacitance (in μ F), capacitance tolerance letter, rated voltage, date code, lot symbol and Vishay trademark.		

SELECTOR GUIDES		
Tantalum Selector Guide	www.vishay.com/doc?49375	
Parameter Comparison Guide	www.vishay.com/doc?42088	

3



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.