

## ROLINE GOLD DisplayPort Cable, DP-DP, M/M, 10.0 m

<b>Product No.</b>	11.04.5649
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	11.04.5649
<b>EAN (single piece)</b>	7611990151080



**ROLINE DisplayPort Cable with DP connection on both sides for connecting an Ultrabook, Notebook/Laptop or PC to a monitor, TV or projector - for screen transmissions in excellent quality with resolutions of up to 4096x2160 @60Hz!**

- DisplayPort is a universal connection standard for the transmission of picture and sound signals. Applications include mainly the connection of monitors and televisions to computers, BluRay players and similar devices.
- The connector requires less space and is therefore more suitable for portable display devices (ultrabooks, notebooks/laptops) or for 2 connectors on a graphics card (on a slot plate).
- The practical plug design prevents the cable from slipping out of the DisplayPort socket.
- The robust nylon braid protects the DisplayPort cable effectively and sets it in scene visually.
- High-quality, double-shielded cable (foil+braid) with gold-plated contacts for optimum transmission of image signals

- Gold connector housing

### **ROLINE GOLD - Top quality without any compromises!**

Cables in ROLINE GOLD quality come with high quality shielding and gilded contacts for contact safety even at high plug-in cycles. The plugs are gold coated to enhance their contact durability. Nylon-reinforced outer material in golden/black provides a better stability and gives the cable a stunning look.

- Compliant DP v1.2 (max. 4096x2160 @60Hz)

#### **Technical specifications**

Manufacturer	ROLINE
Product group	Cable
Product type	DisplayPort Monitor Cable
Colour	black / gold
Length	10 m
Transfer quality	DisplayPort v1.2
Max. resolution	4096x2160 @60Hz
side 1 connector	DisplayPort M
side 2 connector	DisplayPort M
Side 1 Connector Type	DisplayPort
Side 1 Connector Gender	Male
Side 2 Connector Type	DisplayPort
Side 2 Connector Gender	Male
Area of application	External
Cable shielding	Screened