

## ConnectPower CP DC UPS 24V 20A/10A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



The UPS control unit together with the associated battery module and the power supply unit form a complete DC UPS system. In normal operation, the input voltage from the UPS control unit is connected directly to the load. In the event of a mains failure (drop of the DC input voltage) the system switches instantly to battery operation.

Once the mains supply has been restored, the system switches back to normal operation and the battery is fully recharged by the integrated charger.

Three relay outputs, as well as three additional active transistor outputs and a control input to lock battery operation, provide full remote control by means of SPS or DCS control. Numerous modes of operation and an easy-to-use status display provide rapid fault diagnosis and optimum customisation to the application.

### General ordering data

Type	CP DC UPS 24V 20A/10A
Order No.	<a href="#">1370050010</a>
Version	UPS control unit
GTIN (EAN)	4050118202335
Qty.	1 pc(s).

**ConnectPower**  
**CP DC UPS 24V 20A/10A**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	66 mm	Width (inches)	2.598 inch
Height	130 mm	Height (inches)	5.118 inch
Depth	150 mm	Depth (inches)	5.905 inch
Net weight	1,146 Kg		

**Temperatures**

Humidity	5...95 %, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-25 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C	Operating temperature	-25 °C...70 °C
Storage temperature	-40 °C...85 °C		

**Battery module**

Parallel connection option	yes, max 2.	Rated voltage	24 V
Storage medium	1.3 Ah, 3.4 Ah, 7.2 Ah, 12 Ah, 17 Ah, Selectable with rotary switch		

**Integrated battery charger**

Battery availability test	every minute	Charging current	0.15 CA
Charging feature	IU characteristic curve	Charging voltage (temperature compensated)	27.48 V @ 20°C
Temperature coefficient	-48 mV / °C		

**Operating interfaces and control inputs**

DIP switch	Inversion of transistor outputs, Operation without temperature probe	Output current selector switch	20 A, 10 A
Remote disconnection (Interlock)	Yes	Selector switch battery	1.3 Ah, 3.4 Ah, 7.2 Ah, 12 Ah, 17 Ah, No Battery, Service
Selector switch buffer times	0.5 min, 1 min, 3 min, 5 min, 10 min, 20 min, 30 min, 45 min, ∞, ∞ w/0	Temperature probe	NTC 100 kΩ

**Input**

DC current consumption	max. 200 mA (without battery), max. 0.5 A (with fully charged battery)	DC input voltage range	20...30 V DC
Input current	≤ 13A (for 10A), ≤ 23A (for 20A)	Input fuse (internal)	Yes
Max. approved input current	28 A	Rated input voltage	24 V DC
Wire connection method	Screw connection		

## ConnectPower CP DC UPS 24V 20A/10A

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

### Technical data

#### output

Continuous output current @ $U_{Rated}$	24 A @ 45 °C, 20 A @ 60 °C, 15 A @ 70 °C	Output current, max.	24 A
Output voltage	$V_o = V_{in} - 0.2$ V normal operation ( $I_{max}$ ), $V_o = V_{in} - 0.3$ V battery operation ( $I_{max}$ )	Overload protection	Yes
Parallel connection option	yes, max 2., Yes, with diode module	Power reserve at nom. voltage	24 A for 1 min, ED = 5 %
Protection against inverse voltage	Yes	Rated (nominal) output current @ $U_{Nom}$	20 A @ 60 °C
Rated output voltage	24 V DC $\pm$ 1 %	Residual ripple, breaking spikes	< 50 mV <sub>SS</sub> @ 24 V DC, $I_N$
Temperature coefficient	- 48 mV / °C	Temperature probe	NTC 100 k $\Omega$
Wire connection method	Screw connection		

#### General data

Buffer times	Depending on the connected battery	Clip-in foot	metal
Current limiting	> 120 % $I_N$	Degree of efficiency	$\geq$ 96% normal mode, battery is being charged, $\geq$ 98% normal mode, battery is charged, $\geq$ 98% buffer mode
Housing version MTBF	Metal, corrosion resistant > 500,000 h acc. to IEC 1709 (SN29500)	Humidity	5...95 %, no condensation
Operating temperature	-25 °C...70 °C	Mounting position, installation notice	Horizontal on TS35 mounting rail. 50 mm of clearance at top & bottom for air circ. Can mount side by side with no space in between.
Protection against reverse voltages from the load	32...34 V DC	Power loss	< 10 W
Short-circuit protection	Yes	Protection degree	IP20
Surge voltage category	III	Storage medium	1.3 Ah, 3.4 Ah, 7.2 Ah, 12 Ah, 17 Ah, Selectable with rotary switch

#### EMC / shock / vibration

Noise emission acc. to EN55022	Class B	Vibration resistance IEC 60068-2-6	2.3 g
Interference immunity test acc. to	EN 61000-4-2 (ESD)  EN 61000-4-3 and EN 61000-4-8 (fields) EN 61000-4-4 (burst) EN 61000-4-5 (surge) EN 61000-4-6 (conducted)  EN 61000-4-11 (dips)	Shock resistance IEC 60068-2-27	30 g in all directions

#### Insulation coordination

Class of protection	III, with no ground connection, for SELV	Insulation voltage	1 kV DC
Pollution severity	2	Surge voltage category	III
electrical isolation, input-earth	1 kV	electrical isolation, output-earth	1 kV

**ConnectPower  
CP DC UPS 24V 20A/10A**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Electrical safety (applied standards)**

Electrical machine equipment	Acc. to EN60204	For use with electronic equipment	Acc. to EN50178 / VDE0160
Protection against dangerous shock currents	Acc. to VDE0106-101	Protective separation / protection against electrical shock	VDE0100-410 / acc. to DIN57100-410
Safety transformers for switch-mode power supplies	nach EN61558-2-16		

**Connection data (input)**

Conductor cross-section, AWG/kcmil , max.	6	Conductor cross-section, AWG/kcmil , min.	26
Conductor cross-section, flexible , min.	0.5 mm <sup>2</sup>	Conductor cross-section, rigid , max.	16 mm <sup>2</sup>
Conductor cross-section, rigid , min.	0.5 mm <sup>2</sup>	Reverse polarity protection	Yes
Tightening torque, max.	1.5 Nm	Tightening torque, min.	1.2 Nm
Wire connection cross section, flexible (input), max.	16 mm <sup>2</sup>		

**Connection data (output)**

Conductor cross-section, AWG/kcmil , max.	6	Conductor cross-section, AWG/kcmil , min.	26
Conductor cross-section, flexible , max.	16 mm <sup>2</sup>	Conductor cross-section, flexible , min.	0.5 mm <sup>2</sup>
Conductor cross-section, rigid , max.	16 mm <sup>2</sup>	Conductor cross-section, rigid , min.	0.6 mm <sup>2</sup>
Tightening torque, max.	1.5 Nm	Tightening torque, min.	1.2 Nm

**Connection data (signal)**

Wire connection cross-section, flexible (signal), max.	16 mm <sup>2</sup>	Wire connection cross-section, flexible (signal), min.	0.5 mm <sup>2</sup>
Wire connection method	Screw connection	Wire cross-section, AWG/kcmil , max.	12
Wire cross-section, AWG/kcmil , min.	26	Wire cross-section, solid , max.	16 mm <sup>2</sup>
Wire cross-section, solid , min.	0.5 mm <sup>2</sup>		

**Signalling**

Floating contact	Yes	Status indicator	Three-colour LED: battery capacity > 85% green, > 40% yellow, > 20% red, < 20% red (blinking), Green/yellow LED: normal / buffering, Yellow/red LED: temperature alarm / alarm, Yellow/red LED: switch-off / battery fault
Status relay (max. load)	Fault (alarm) (30 V AC/DC 0.1 A), Battery operation (buff.) (30 V AC/DC 0.1 A), Laden (Charg.) (30V AC/DC 0,1A)		



**Data sheet**

**ConnectPower  
CP DC UPS 24V 20A/10A**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Approvals**

Institute (GERMLLOYD)		Certificate No. (GERMLLOYD)	61934-14
Institute (cULus)		Certificate no. (cULus)	E258476

**Classifications**

ETIM 6.0	EC002850	eClass 6.2	27-04-06-03
eClass 7.1	27-04-06-03	eClass 8.1	27-04-06-03
eClass 9.0	27-04-06-03	eClass 9.1	27-04-92-01

**Approvals**

Approvals	
ROHS	Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">DE_PA5200_160310_004.pdf</a>
Brochure/Catalogue	<a href="#">CAT 4.3 ELECTR 15/16 EN</a>
Engineering Data	<a href="#">EPLAN_WSCAD</a>
User Documentation	<a href="#">Operating instructions</a>