

**ConnectPower  
CP A BATTERY 24V DC3.4AH**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The Weidmüller battery modules consist of high-quality Panasonic batteries. These are sealed, maintenance-free lead-fleece batteries. The battery modules are fitted with a temperature sensor to provide optimum battery charging and battery life. This facilitates temperature-compensated charging of the batteries.

The neat design as well as the plug-in connections for the battery connection and the temperature sensor allow the batteries to be fitted safely and quickly.

**General ordering data**

Type	CP A BATTERY 24V DC3.4AH
Order No.	<a href="#">1251070000</a>
Version	Battery
GTIN (EAN)	4050118043105
Qty.	1 pc(s).

**ConnectPower  
CP A BATTERY 24V DC3.4AH**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	108 mm	Width (inches)	4.252 inch
Height	144 mm	Height (inches)	5.669 inch
Depth	137 mm	Depth (inches)	5.394 inch
Net weight	10 g		

**Temperatures**

Operating temperature, max.	40 °C	Operating temperature, min.	0 °C
Storage temperature, max.	40 °C	Storage temperature, min.	-15 °C
Operating temperature	0 °C...40 °C	Ambient temperature	0°...+40°C (Charging); -15°...+50°C (Discharging)
Storage temperature	-15 °C...40 °C		

**Operating interfaces and control inputs**

Temperature probe	NTC 100 kΩ
-------------------	------------

**Input**

Charging current, max.	0.51 A	Nominal capacity	3.4 Ah
Rated input voltage	24 V DC		

**output**

Buffer time 10A	11.3 min	Buffer time 20A	5 min
Output current, max.	25 A	Overload and short circuit protection	25 A fuse
Parallel connection option	Yes	Protection against inverse voltage	Yes
Temperature probe	NTC 100 kΩ		

**General data**

Battery type	Maintenance-free AGM lead-acid battery	Clip-in foot	metal
Latest commissioning	9 months	Max. perm. air humidity (operational)	5 %...95 % RH
Operating life	6...9 years @ 20°C	Operating temperature	0 °C...40 °C
Protection degree	IP20	Series switching capability	No
Shock wall acc. to IEC 68227	30 g	Vibration DIN rail/wall in accordance with IEC 68-2-6	0.7 / 0.7 g

**Insulation coordination**

Class of protection	III, with no ground connection, for SELV
---------------------	--

**Connection data (input)**

Conductor cross-section, AWG/kcmil , max.	10	Conductor cross-section, AWG/kcmil , min.	22
Conductor cross-section, flexible , min.	0.5 mm <sup>2</sup>	Conductor cross-section, rigid , max.	6 mm <sup>2</sup>
Conductor cross-section, rigid , min.	0.2 mm <sup>2</sup>	Tightening torque, max.	0.6 Nm
Tightening torque, min.	0.5 Nm	Wire connection cross section, flexible (input), max.	6 mm <sup>2</sup>

## ConnectPower CP A BATTERY 24V DC3.4AH

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Connection data (output)

Conductor cross-section, AWG/kcmil , max.	10	Conductor cross-section, AWG/kcmil , min.	22
Conductor cross-section, flexible , max.	6 mm <sup>2</sup>	Conductor cross-section, flexible , min.	0.5 mm <sup>2</sup>
Conductor cross-section, rigid , max.	6 mm <sup>2</sup>	Conductor cross-section, rigid , min.	0.2 mm <sup>2</sup>
Number of terminals	2 (+ / -)	Tightening torque, max.	0.6 Nm
Tightening torque, min.	0.5 Nm		

### Connection data (signal)

Number of terminals	2	Wire connection cross-section, flexible (signal), max.	1.5 mm <sup>2</sup>
Wire connection cross-section, flexible (signal), min.	0.2 mm <sup>2</sup>	Wire connection method	Pluggable screw connection
Wire cross-section, AWG/kcmil , max.	16	Wire cross-section, AWG/kcmil , min.	28
Wire cross-section, solid , max.	1.5 mm <sup>2</sup>	Wire cross-section, solid , min.	0.2 mm <sup>2</sup>

### Approvals

Institute (GERMLLOYD)		Certificate No. (GERMLLOYD)	
			61934-14
Institute (cULus)		Certificate no. (cULus)	
			E354601

### Classifications

ETIM 6.0	EC002850	eClass 6.2	27-04-06-03
eClass 7.1	27-04-06-03	eClass 8.1	27-04-06-03
eClass 9.0	27-04-06-03	eClass 9.1	27-04-92-01

### Approvals

Approvals			
ROHS	Conform		

### Downloads

Brochure/Catalogue	<a href="#">CAT 4.3 ELECTR 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
User Documentation	<a href="#">Operating instructions</a>