



2MP HD-TVI Eyeball Cameras with Junction Box

VLDT4G

3.6mm fixed lens, dark gray housing

VLDT4W

3.6mm fixed lens, white housing



Features

- 1/2.9" 2MP Sony CMOS
- Supports multiple video signal outputs (TVI / AHD / CVI / CVBS)*
- 18 built-in IR LEDs
- IP66 compliant, weather resistant
- Full OSD operation through onboard control and UTC (up the coax)
- Junction box included
- UL Listed
- 5 year warranty



Camera Specifications

| | |
|--------------------------|----------------------------------------------|
| Image Sensor | 1/2.9" 2MP Sony CMOS |
| Maximum Resolution | 1920x1080 |
| Minimum Illumination | 0 lux |
| Number of IR LEDs | 18 |
| IR Distance | Up to 65 ft. (depending on scene reflection) |
| White Balance | ATW |
| Blacklight Compensation | Auto |
| Electronic Shutter Speed | NTSC: 1/60-1/100,000 PAL: 1/50-1/100,000 |
| AGC | On/Off |
| DNR | On/Off |
| WDR | On/Off |
| Day/Night | Auto / Color / BW / EXT |
| OSD | UTC |
| Gamma | 0.45 typ. |
| Scanning System | Progressive |
| Video Signal Output | HD-TVI / AHD / CVI / CVBS |

Operating Specifications

| | |
|-----------------------|-----------------------------------|
| Power Supply | 12VDC (power supply not included) |
| Power Consumption | Max. 400mA |
| Operating Temperature | -22°F - 104°F |
| Storage Temperature | -22°F - 104°F |
| Unit Dimensions | 3.7" (W) x 3.15" (H) |
| Unit Weight | 11.64 oz. |

Optional Accessories



TVIUTPPT
HD Video Transceiver
with Pigtail (Balun)



TVIUTP
HD Video
Transceiver



PSW5
12VDC
Power Supply

*Cameras are defaulted to HD-TVI. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 12/11/17