





< List of part numbers with package codes > B1047AS-221M=P3

Shape

Image: second system Image: second system

Notes

Rated current (lsat) is specified when the decrease of the initial inductance value at 30%. (The ambient reference temperature is 20°C.) Rated current (Itemp) is specified when temperature of inductor the is raised 40°C by DC current. (The ambient reference temperature is 20°C.)

References

Packaging code	Specifications	Minimum quantity
=P3	φ330mm Embossed taping	1000

Mass (Typ.)	
1 piece	0.975g

Specifications

Inductance	220μH ±20%
Inductance test frequency	0.1MHz
Rated current (Isat) (Based on Inductance change)	620mA
Rated current (Itemp) (Based on Temperature rise)	470mA
Max. of DC resistance	1.100Ω
Operating temperature range (Self-temperature rise is included)	-40~85°C
Class of magnetic shield	Ferrite Core
Series	DS75LC

🔔 Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.


2. This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



1 of 2

Chart of characteristic data (The charts below may show another part number which shares its characteristics.)





🔔 Attention

 This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
 This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.