


# OMNIMATE Power - series LX

## LX 15.00/05/90 4.5SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



High-performance PCB terminal with proven clamping yoke connection at 15.00 mm pitch, conductor outlet direction in 90° design. Version and test point

- 1.50 - 25 mm<sup>2</sup> (IEC) / 16 - 4 AWG (UL)
- 1000 V (IEC) / 600 V (UL)
- 101 A (IEC) / 85 A (UL)

### General ordering data

|              |                                                                                                                                                                       |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type         | LX 15.00/05/90 4.5SN BK BX                                                                                                                                            |
| Order No.    | <a href="#">1226490000</a>                                                                                                                                            |
| Version      | PCB terminal, 15.00 mm, No. of poles: 5, 90°, Solder pin length (l): 4.5 mm, tinned, Black, Clamping yoke connection, Clamping range, max. : 25 mm <sup>2</sup> , Box |
| GTIN (EAN)   | 4050118011128                                                                                                                                                         |
| Qty.         | 20 pc(s).                                                                                                                                                             |
| Product data | IEC: 1000 V / 101 A / 1.5 - 25 mm <sup>2</sup><br>UL: 600 V / 85 A / AWG 16 - AWG 4                                                                                   |
| Packaging    | Box                                                                                                                                                                   |

## OMNIMATE Power - series LX LX 15.00/05/90 4.5SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 85.5 g |
|------------|--------|

### System parameters

|                                                    |                            |                                              |                          |
|----------------------------------------------------|----------------------------|----------------------------------------------|--------------------------|
| Product family                                     | OMNIMATE Power - series LX | Wire connection method                       | Clamping yoke connection |
| Mounting onto the PCB                              | THT solder connection      | Conductor outlet direction                   | 90°                      |
| Pitch in mm (P)                                    | 15 mm                      | Pitch in inches (P)                          | 0.591 inch               |
| No. of poles                                       | 5                          | Fitted by customer                           | No                       |
| Max. adjacent poles per row                        | 10                         | Solder pin length (l)                        | 4.5 mm                   |
| Solder pin dimensions                              | 1.2 x 1.2 mm               | Solder eyelet hole diameter (D)              | 1.6 mm                   |
| Solder eyelet hole diameter tolerance (D) + 0,1 mm |                            | Number of solder pins per pole               | 2                        |
| Screwdriver blade                                  | 1.0 x 5.5                  | Screwdriver blade standard                   | DIN 5264                 |
| Tightening torque, min.                            | 2.4 Nm                     | Tightening torque, max.                      | 4 Nm                     |
| Clamping screw                                     | M 5                        | Stripping length                             | 16 mm                    |
| L1 in mm                                           | 60 mm                      | L1 in inches                                 | 2.362 inch               |
| Touch-safe protection acc. to DIN VDE 0470         | IP 10                      | Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch   |
| Volume resistance                                  | 0.50 mΩ                    |                                              |                          |

### Material data

|                                       |            |                                       |                              |
|---------------------------------------|------------|---------------------------------------|------------------------------|
| Insulating material                   | Wemid (PA) | Colour                                | Black                        |
| Colour chart (similar)                | RAL 9011   | Insulating material group             | I                            |
| CTI                                   | ≥ 600      | Insulation resistance                 | ≥ 10 <sup>8</sup> Ω          |
| UL 94 flammability rating             | V-0        | Contact material                      | E-Cu                         |
| Contact surface                       | tinned     | Layer structure of solder connection  | 1.5-3 µm Ni / 4-6 µm Sn matt |
| Storage temperature, min.             | -25 °C     | Storage temperature, max.             | 55 °C                        |
| Max. relative humidity during storage | 80 %       | Operating temperature, min.           | -50 °C                       |
| Operating temperature, max.           | 120 °C     | Temperature range, installation, min. | -25 °C                       |
| Temperature range, installation, max. | 120 °C     |                                       |                              |

### Conductors suitable for connection

|                                                 |                      |                                                 |                    |
|-------------------------------------------------|----------------------|-------------------------------------------------|--------------------|
| Clamping range, min.                            | 1.31 mm <sup>2</sup> | Clamping range, max.                            | 25 mm <sup>2</sup> |
| Wire connection cross section AWG, min.         | AWG 16               | Wire connection cross section AWG, max.         | AWG 4              |
| Solid, min. H05(07) V-U                         | 1.5 mm <sup>2</sup>  | Solid, max. H05(07) V-U                         | 16 mm <sup>2</sup> |
| Stranded, min. H07V-R                           | 6 mm <sup>2</sup>    | Stranded, max. H07V-R                           | 25 mm <sup>2</sup> |
| Flexible, min. H05(07) V-K                      | 1.5 mm <sup>2</sup>  | Flexible, max. H05(07) V-K                      | 25 mm <sup>2</sup> |
| w. plastic collar ferrule, DIN 46228 pt 4, min. | 1.5 mm <sup>2</sup>  | w. plastic collar ferrule, DIN 46228 pt 4, max. | 16 mm <sup>2</sup> |
| w. wire end ferrule, DIN 46228 pt 1, min.       | 1.5 mm <sup>2</sup>  | w. wire end ferrule, DIN 46228 pt 1, max.       | 16 mm <sup>2</sup> |
| Plug gauge acc. to EN 60999 a x b; Ø            | 6.9 mm x 6.9 mm      |                                                 |                    |

**OMNIMATE Power - series LX**  
**LX 15.00/05/90 4.5SN BK BX**
**Weidmüller Interface GmbH & Co. KG**

 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Rated data acc. to IEC**

|                                                                           |                        |                                                                       |                   |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. no. of poles (Tu=20°C)                            | 101 A             |
| Rated current, max. no. of poles (Tu=20°C)                                | 101 A                  | Rated current, min. no. of poles (Tu=40°C)                            | 101 A             |
| Rated current, max. no. of poles (Tu=40°C)                                | 101 A                  | Rated voltage for surge voltage class / pollution degree II/2         | 1,000 V           |
| Rated voltage for surge voltage class / pollution degree III/2            | 1,000 V                | Rated voltage for surge voltage class / pollution degree III/3        | 1,000 V           |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 6 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 8 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 8 kV                   | Short-time withstand current resistance                               | 3 x 1s mit 1000 A |

**Rated data acc. to CSA**

|                               |        |                               |       |
|-------------------------------|--------|-------------------------------|-------|
| Rated voltage (Use group B)   | 600 V  | Rated voltage (Use group C)   | 600 V |
| Rated voltage (use group D)   | 600 V  | Rated current (use group B)   | 85 A  |
| Rated current (use group C)   | 85 A   | Rated current (use group D)   | 5 A   |
| Wire cross-section, AWG, min. | AWG 16 | Wire cross-section, AWG, max. | AWG 4 |

**Rated data acc. to UL 1059**

|                               |                                                                                     |                               |        |
|-------------------------------|-------------------------------------------------------------------------------------|-------------------------------|--------|
| Institute (UR)                |  | Certificate No. (UR)          | E60693 |
| Rated voltage (use group B)   | 600 V                                                                               | Rated voltage (use group C)   | 600 V  |
| Rated voltage (use group D)   | 600 V                                                                               | Rated current (use group B)   | 85 A   |
| Rated current (use group C)   | 85 A                                                                                | Rated current (use group D)   | 5 A    |
| Wire cross-section, AWG, min. | AWG 16                                                                              | Wire cross-section, AWG, max. | AWG 4  |
| Reference to approval values  | Specifications are maximum values, details - see approval certificate.              |                               |        |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001284    | ETIM 4.0   | EC002643    |
| ETIM 5.0   | EC002643    | ETIM 6.0   | EC002643    |
| eClass 6.2 | 27-26-11-01 | eClass 7.1 | 27-44-04-01 |
| eClass 8.1 | 27-44-04-01 | eClass 9.0 | 27-44-04-01 |
| eClass 9.1 | 27-44-04-01 |            |             |

## OMNIMATE Power - series LX LX 15.00/05/90 4.5SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Notes

#### Notes

- Additional colours on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- The test point can only be used as potential-pickup point.

#### IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

### Approvals

#### Approvals



#### ROHS

Conform

### Downloads

#### Approval/Certificate/Document of Conformity

[Declaration of the Manufacturer](#)

#### Brochure/Catalogue

[FL DRIVES EN](#)  
[MB DEVICE MANUF. EN](#)  
[FL DRIVES DE](#)  
[CAT 2 PORTFOLIOGUIDE EN](#)  
[FL APPL. INVERTER EN](#)  
[FL\\_BASE\\_STATION\\_EN](#)  
[FL ELEVATOR EN](#)  
[FL POWER SUPPLY EN](#)  
[FL 72H SAMPLE SER EN](#)  
[PO OMNIMATE EN](#)

#### Engineering Data

[EPLAN, WSCAD](#)

#### Motion controllers white paper

[Download Whitepaper](#)

#### White Paper UL 600 V


[Download Whitepaper](#)

## OMNIMATE Power - series LX LX 15.00/05/90 4.5SN BK BX


**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

# Drawings


## Dimensional drawing



## Graph




## Graph




## Recommended wave soldering profiles

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

### Single Wave:



### Double Wave:



### Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260°C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.