



# Classic filament LED Lamps

## CLA LEDBulb ND 7-60W E27 WW ST64 CL

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap-Base	E27 [ E27]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	7-60W
Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	806 lm
Luminous Flux (Rated) (Nom)	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (Rated) (Nom)	115.14 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	7 W

Lamp Current (Nom)	60 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	7 kWh


# Classic filament LED Lamps

## Product Data

Full product code	871869674275400
Order product name	CLA LEDBulb ND 7-60W E27 WW ST64 CL
EAN/UPC - Product	8718696742754
Order code	929001387602
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001387602
Net Weight (Piece)	0.048 kg



## Dimensional drawing




Bulb ST64 230V 7-60W 806lm 2700K E27 ND

Product	D	C
CLA LEDBulb ND 7-60W E27 WW ST64 CL	64 mm	140 mm

## Photometric data




LEDbulb 60W E27 827 CL A60 ND




LEDbulb 60W E27 827 CL A60 ND

# Classic filament LED Lamps

## Lifetime



LEDbulb 60W E27 827 CL A60 ND



LEDbulb 60W E27 827 CL A60 ND

