



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207  
Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

[Request a Sample](#)

# Customer Specification

## PART NO. B953602

Construction

		Diameters (In)
1) Component 1	60 X 1 COND	
a) Conductor	24 (7/32) AWG TC	0.024
b) Insulation	0.010" Wall, Nom. PVC, Semi Rigid	0.044
(1) Color Code	Alpha Wire Color Code E	

Cond	Color	Cond	Color	Cond	Color
1	BLACK	21	WHITE/BLACK/RED	41	WHITE/ORANGE/YELLOW
2	BROWN	22	WHITE/BLACK/ORANGE	42	WHITE/ORANGE/GREEN
3	RED	23	WHITE/BLACK/YELLOW	43	WHITE/ORANGE/BLUE
4	ORANGE	24	WHITE/BLACK/GREEN	44	WHITE/ORANGE/VIOLET
5	YELLOW	25	WHITE/BLACK/BLUE	45	WHITE/ORANGE/SLATE
6	GREEN	26	WHITE/BLACK/VIOLET	46	WHITE/YELLOW/GREEN
7	BLUE	27	WHITE/BLACK/SLATE	47	WHITE/YELLOW/BLUE
8	VIOLET	28	WHITE/BROWN/RED	48	WHITE/YELLOW/VIOLET
9	SLATE	29	WHITE/BROWN/ORANGE	49	WHITE/YELLOW/SLATE
10	WHITE	30	WHITE/BROWN/YELLOW	50	WHITE/GREEN/BLUE
11	WHITE/BLACK	31	WHITE/BROWN/GREEN	51	WHITE/GREEN/VIOLET
12	WHITE/BROWN	32	WHITE/BROWN/BLUE	52	WHITE/GREEN/SLATE
13	WHITE/RED	33	WHITE/BROWN/VIOLET	53	WHITE/BLUE/VIOLET
14	WHITE/ORANGE	34	WHITE/BROWN/SLATE	54	WHITE/BLUE/SLATE
15	WHITE/YELLOW	35	WHITE/RED/ORANGE	55	WHITE/VIOLET/SLATE
16	WHITE/GREEN	36	WHITE/RED/YELLOW	56	WHITE/BLACK/BROWN/RED
17	WHITE/BLUE	37	WHITE/RED/GREEN	57	WHITE/BLACK/BROWN/ORANGE

18	WHITE/VIOLET	38	WHITE/RED/BLUE	58	WHITE/BLACK/BROWN/YELLOW
19	WHITE/SLATE	39	WHITE/RED/VIOLET	59	WHITE/BLACK/BROWN/GREEN
20	WHITE/BLACK/BROWN	40	WHITE/RED/SLATE	60	WHITE/BLACK/BROWN/BLUE
2) Cable Assembly		60 Components Cabled			
a) Twists:		2.5 Twists/foot (min)			
b) Core Wrap		Clear Mylar Tape, 25% Overlap, Min.			
3) Shield:		Alum/Mylar Tape, 25% Overlap, Min.			
a) Foil Direction		Foil Facing In			
b) Drain Wire		24 (7/32) AWG TC			
4) Jacket		0.032" Wall, Nom.,PVC		0.467 (0.494 Max.)	
a) Color(s)		GREY			
b) Ripcord		1 End 810 Denier Nylon			
c) Print		ALPHA WIRE-* P/N B953602 0.23MM2 (24AWG) (UL) TYPE CM 105C OR AWM 2464 VW-1 --- LLXXXXXX CSA 105C TYPE CMG FT4 CE ROHS (SEQ METERS) * = Factory Code <i>[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]</i>			

## Applicable Specifications

1) UL		
a) Component 1	AWM/STYLE 10002	105°C / 300 V <sub>RMS</sub>
b) Overall	AWM/STYLE 2464	80°C / 300 V <sub>RMS</sub>
	CM	105°C
	VW-1	
2) CSA International	CMG	105°C
	FT4	
3) IEC	EN 60332-1 Flame Behavior	
	EN 60332-2 Flame Behavior	
4) CE:	EU Low Voltage Directive 2006/95/EC	

## Environmental

1) CE: EU Directive 2011/65/EU(RoHS2):	
	This product complies with European Directive 2011/65/EU (RoHS Directive) of the European Parliament and of the Council of 8 June 2011. No Exemptions are required for RoHS Compliance on this item. Consult Alpha Wire's web site for RoHS C of C.
2) REACH Regulation (EC 1907/2006):	
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration.

## Properties

Physical & Mechanical Properties	
1) Temperature Range	-30 to 105°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	215 Lbs, Maximum
4) Sunlight Resistance	Yes
Electrical Properties	
(For Engineering purposes only)	
1) Voltage Rating	300 V <sub>RMS</sub>
2) Capacitance	32 pf/ft @1 kHz, Nominal Conductor to Conductor
3) Ground Capacitance	58 pf/ft @1 kHz, Nominal
4) Inductance	0.19 µH/ft, Nominal
5) Conductor DCR	26 Ω/1000ft @20°C, Nominal
6) OA Shield DCR	11.6 Ω/1000ft @20°C, Nominal

## Other

<b>Packaging</b>	Flange x Traverse x Barrel (inches)
a) 3280 FT	36 x 14 x 12 Continuous length
b) 1640 FT	30 x 14 x 12 Continuous length
c) 328 FT	16 x 11 x 8 Continuous length
d) 164 FT	12 x 10 x 5 Continuous length
	<i>[Spool dimensions may vary slightly]</i>

www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207  
Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

### ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY

Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document. ©2013 ALPHA WIRE - all rights reserved.



# EU/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: B953602

B953602 , RoHS-Compliant Commencing With 7/13/2011 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3) The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item.** Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014.

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm )
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE) ,	
Including Deca-BDE	0.1% by weight (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% by weight (1000 ppm)
Butyl benzyl phthalate (BBP)	0.1% by weight (1000 ppm)
Dibutyl phthalate (DBP)	0.1% by weight (1000 ppm)
Diisobutyl phthalate (DIBP)	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering & QA

5/24/2018

Alpha Wire

711 Lidgerwood Ave.

Elizabeth, NJ 07207

Tel: 1-908-925-8000