



Main

Range	TeSys
Product name	TeSys GS
Device short name	GS2EU
Product or component type	Switch-disconnector-fuse
Poles description	3P
Protected poles description	3t
Contacts type and composition	3 NO
[I _{th}] conventional free air thermal current	30 A at 40 °C
[I _e] rated operational current	30 A
Fuse type	UL
Fuse size	J
Network type	AC DC
Network frequency	50/60 Hz

Complementary

Type of operating handle	External frontal
Mounting support	Plate Rail
[U _i] rated insulation voltage	750 V
[U _{imp}] rated impulse withstand voltage	8 kV
Rated operational power in W	15 kW at 400 V 25 kW at 690 V 18.5 kW at 500 V
Short-circuit withstand	17.6 kA
Mechanical durability	10000 cycles
Electrical durability	6000 cycles
Connections - terminals	Power circuit : lugs-ring terminals cable 2...13 mm ²
Tightening torque	Power circuit : 6.6 N.m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	UL98 CSA C22.2 No 4
IP degree of protection	IP20 with terminal cover conforming to IEC 60529
Ambient air temperature for operation	-20...70 °C
Ambient air temperature for storage	-40...80 °C
Fire resistance	960 °C body
Height	136 mm
Width	149.3 mm
Depth	123 mm

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1650 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold