BL654 Series

Bluetooth® v5 + 802.15.4 + NFC Modules & Adapter



SECURE, POWERFUL WIRELESS ENGINE FOR YOUR IOT DESIGN



Building on Laird's expertise with Nordic from the BL600 and BL652 series comes the most powerful yet - the BL654 series! It provides OEMs with the maximum design flexibility and performance. A complete multi-protocol embedded wireless offering with exceptional processing capability, all at a micro power budget.

Powered by Nordic's nRF52840 silicon, the small form factor BL654 modules, DVKs and USB Dongle provide for a secure, robust BLE and Cortex -M4F CPU for any OEM's product design. The BL654 provides you with maximum development flexibility with programming options for the Nordic SDK, a simple, intuitive AT Command Set, as well as Laird's own **smartBASIC** environment.

The BL654 series brings out all nRF52840 hardware features and capabilities including **USB access**, up to **5.5V** supply considerations, and 802.15.4 (Thread) implementation. Complete regulatory certifications enable faster time to market and reduced development risk completes Laird's simplification of your next Bluetooth design!



- Bluetooth v5 Bluetooth Low Energy (BLE) plus NFC
- **Thread** 802.15.4 functionality (via Nordic SDK)
- Widest range of configurable interfaces: UART, I2C, SPI, ADC, GPIO, PWM, FREQ, USB, and NFC
- Industrial Temp Rating (-40° to +85° C)
- **Ultra-Small footprint** (15mm x 10mm x 2.2mm)
- BLE Peripheral/Central roles with DTM embedded
- 2Mbps & LE Long Range: Support for 2Mbps, 1Mbps, & 125kps coded
- Hostless operation Internal MCU reduces BOM
- Powerful Core Cortex-M4F (1Mbit Flash, 256k RAM)
- Built on years of experience with Nordic (BL600 & BL652
- **Fully featured development kit** everything needed to start BLE development
- **Application Design Choice:** Leverage Laird's smartBASIC, simple AT Command Set or utilize Nordic SDK directly.
- USB Dongle option: Packaged USB Adapter bring full Bluetooth v5 connectivity to ANY device with a virtual COM port capability

Features at a Glance



TRULY HOSTLESS OPERATION FOR AUTOMATED USE CASES

Combine on-module MCU, smartBASIC and simultaneous central/peripheral role support for a powerful hostless solution for sensor applications.

SPEED TO MARKET



Easily write event-driven, automated applications, no toolchain required with smartBASIC. Or utilize the Nordic SDK directly – design your way



EXTREMELY EFFICIENT POWER MANAGEMENT

Customize to balance throughput with power usage, enabled by ultra-low power sleep mode.



GLOBAL APPROVALS - MAKE YOURSELF AT HOME

Carries several modular FCC, IC, CE, RCM, MIC and Bluetooth SIG approvals.



PERSONAL SUPPORT FROM DESIGN TO MANUFACTURE

Laird's industry-renowned support is passionate about helping you speed your design to market.

Application areas



IoT Devices and Sensors



Beacons and Proximity **Applications**



Secure Medical Peripherals



Industrial Monitoring

Contact Sales -Americas: +1 262 375 4400

+44 1628 940 ext. 958 Europe:

Korea: +82 10 2622 3935 Hong Kong: +852 2923 0610

For documentation, software, sample apps and more visit: http://www.lairdtech.com/products/bl654-ble-thread-nfc-modules

Laird BL654 Bluetooth® 5 + 802.15.4 + NFC Product Series

Product Brief



Key Specifications

Category	Feature	Specification
Wireless	Bluetooth®	v5 – Single-Mode (Peripheral and Central Roles)
Specification	Thread®	802.15.4 stack provided via Nordic SDK
	Frequency	2.402 - 2.480 GHz
	Transmit Power	+ 8 dBm (maximum). Configurable down to -40 dBm
	Receive Sensitivity	-95 dBm (typical @ BLE 1 Mpbs)
		-92 dBm (typical @ BLE 2 Mbps
		-103 dBm (typical @ BLE 125 kbps)
	Link Budget	103 dB (@ BLE Mbps), 111 db (@ BLE 125kpbs)
	Antenna Options	PCB Trace antenna or IPEX MHF4 RF Connector
	Raw Data Rates (Air)	1 Mbps, 2 Mbps, 125kbps
Host Interface and Peripherals	UART Interface	TX, RX, CTS, RTS. DTR, DSR, DCD, RI possible in smartBASIC (GPIO) Default: 115200, N, 8, 1. Configurable from 1200 bps to 1 Mbps
	USB Interface	2 pins - CDC/Audio/HID & Mass storage virtual interfaces
	Other	48 multifunction GPIO's that can provide: 2 UART (4 GPIO pins each) 2 PDM (2 GPIO pins each)
		 8 ADC channels (1 pin each) 2 PDM (2 GFIO pins each) 2 12S (5 GPIO pins)
		 2 I2C (2 GPIO pins each) 2 GPIO pins for 32.768kHz crystal
		 4 SPI Master (4 GPIO pins 2 GPIO pins for NFC
		including CS each) • PWM output on 16 pins
		 1 QSPI (6 GPIO pins) FREQ output on 16 pins
Key BLE Features	Bluetooth Low Energy	GATT Client & GATT Server – Any LE Advertising Extensions
	blocioonii Lovv Ericigy	Adopted / Custom Services • LE Secure Connections
		 Central / Peripheral Roles. Data Packet Length Extensions
		 Up to 20 BLE connections LE Privacy v1.2
		BLE MeshLE Ping
		 CODED PHY vSP – Virtual Serial Port
		• 2M PHY
Programmability Options	smartBASIC	On-board BASIC programming language
	AT Command Set	Simple AT 'Hayes style' command protocol
	Nordic SDK	Software / Support available from Nordic directly
FW upgrade	THORAGE OBTA	Via UART or JTAG
Supply Voltage		1.7V – 5.5V
Power Consumption	Current	Max Peak Radio Current (@ +8dBm TX) – 14.1mA (DCDC at 3V)
Tower Consumption	33113111	Max Peak Radio Current (@ 0dBm TX) - 4.9mA (DCDC at 3V)
		Standby Doze – TBC µA
		Deep Sleep -0.4µA (external signal wake up)
Physical	Dimensions	15mm x 10mm x 2.2mm (Modules)
i iiyalcui	DITTICT ISIOUS	18.39 mm x 50.74 mm x 11mm (USB Adapter)
Environmental	Temp Range	-40°C to +85°C
Miscellaneous	Lead Free	Lead-free and RoHS compliant
	Development Kit	Development board and free software tools
Development Tools	Utilities	UwTerminalX (Multi-platform)
	Offilles	Android and iOS applications
		UART firmware upgrade
Qualifications	Bluetooth®	Complete Declaration ID (pending)
		FCC / IC / CE / MIC / RCM - All BL654 Series (pending)
Regulator	Approvals	ICC / IC / CE / MIC / KCM - All bloo4 selles (perialing)

For full specifications on BL654 modules, please see the appropriate datasheet.

Part #	Description		
451-00001	Bluetooth v5 + 802.15.4 + NFC Module – Integrated Antenna		
451-00002	Bluetooth v5 + 802.15.4 + NFC Module – IPEX MHF4 Antenna Connector		
451-00003	Intelligent USB Bluetooth v5 Adapter		
455-00001	Development Board for Bluetooth v5 + 802.15.4 + NFC Module – Integrated Antenna		
455-00002	Development Board for Bluetooth v5 + 802.15.4 + NFC Module – IPEX MHF4 Antenna Connector		

Korea: +82 10 2622 3935

Hong Kong: +852 2923 0610