



## OMNIMATE Signal - series BC/SC 3.81 SCZ 3.81/12/180F SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The inverted SCZ pin plug with clamping-yoke screw connection is designed for straight wire connections in 3.81-mm pitch. It can be used in two ways:

- for wire-to-wire connections together with the BCZ
- as a mating plug for the touch-safe BCL socket block on the PCB.

The SCZ is available in four different versions:

- Without flange ("G", closed)
- With standard flange ("F", with socket nut)
- With inverted flange ("FI", with screw)
- and with Weidmüller's patented release latch for a tool-free, no-strain disconnect

The SCZ provides space for labelling and can be coded.

### General ordering data

|              |   |
|--------------|---|
| Type         | SCZ 3.81/12/180F SN OR BX   |
| Order No.    | <a href="#">1971020000</a>  |
| Version      | PCB plug-in connector, male plug, 3.81 mm, No. of poles: 12, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm², Box |
| GTIN (EAN)   | 4032248680832   |
| Qty.         | 50 pc(s).   |
| Product data | IEC: 320 V / 17.5 A / 0.2 - 1.5 mm²<br>UL: 300 V / 10 A / AWG 28 - AWG 16   |
| Packaging    | Box   |

**OMNIMATE Signal - series BC/SC 3.81  
SCZ 3.81/12/180F SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |
|------------|---------|
| Net weight | 11.22 g |
|------------|---------|

**System parameters**

| Product family                               |                          | Type of connection                         |                   |
|--|--------------------------|--|-------------------|
| OMNIMATE Signal - series BC/SC 3.81          |                          | Field connection                           |                   |
| Wire connection method                       | Clamping yoke connection | Pitch in mm (P)                            | 3.81 mm           |
| Pitch in inches (P)                          | 0.15 inch                | Conductor outlet direction                 | 180°              |
| No. of poles                                 | 12                       | L1 in mm                                   | 41.91 mm          |
| L1 in inches                                 | 1.65 inch                | Number of rows                             | 1                 |
| Pin series quantity                          | 1                        | Rated cross-section                        | 1 mm <sup>2</sup> |
| Touch-safe protection acc. to DIN VDE 57 106 |                          | Touch-safe protection acc. to DIN VDE 0470 |                   |
| Safe from finger touch                       |                          | IP 20                                      |                   |
| Volume resistance                            | 6.00 mΩ                  | Can be coded                               | Yes               |
| Stripping length                             | 7 mm                     | Tightening torque for screw flange, min.   | 0.2 Nm            |
| Tightening torque for screw flange, max.     | 0.3 Nm                   | Tightening torque, min.                    | 0.2 Nm            |
| Tightening torque, max.                      | 0.25 Nm                  | Clamping screw                             | M 2               |
| Screwdriver blade                            | 0.4 x 2.5                | Screwdriver blade standard                 | DIN 5264-A        |
| Plugging cycles                              | 25                       | push-in force/pole                         | 0 N               |
| Packaging                                    | Box                      |  |                   |

**Material data**

| Insulating material                   |          | Colour                                |                     |
|---------------------------------------|----------|---------------------------------------|---------------------|
| PA GF                                 |          | Orange                                |                     |
| Colour chart (similar)                | RAL 2000 | Insulating material group             | II                  |
| CTI                                   | ≥ 550    | Insulation resistance                 | ≥ 10 <sup>8</sup> Ω |
| UL 94 flammability rating             | V-0      | Layer structure of plug contact       | 4-8 μm Sn           |
| Storage temperature, min.             | -25 °C   | Storage temperature, max.             | 55 °C               |
| Max. relative humidity during storage | 80 %     | Operating temperature, min.           | -50 °C              |
| Operating temperature, max.           | 120 °C   | Temperature range, installation, min. | -25 °C              |
| Temperature range, installation, max. | 120 °C   |                                       |                     |

**Conductors suitable for connection**

| Clamping range, min.                            |                          | Clamping range, max.                            |                     |
|---|--------------------------|---|---------------------|
| 0.08 mm <sup>2</sup>                            |                          | 1.5 mm <sup>2</sup>                             |                     |
| Wire connection cross section AWG, min.         | AWG 28                   | Wire connection cross section AWG, max.         | AWG 16              |
| Solid, min. H05(07) V-U                         | 0.2 mm <sup>2</sup>      | Solid, max. H05(07) V-U                         | 1.5 mm <sup>2</sup> |
| Flexible, min. H05(07) V-K                      | 0.2 mm <sup>2</sup>      | Flexible, max. H05(07) V-K                      | 1.5 mm <sup>2</sup> |
| w. plastic collar ferrule, DIN 46228 pt 4, min. | 0.2 mm <sup>2</sup>      | w. plastic collar ferrule, DIN 46228 pt 4, max. | 1.5 mm <sup>2</sup> |
| w. wire end ferrule, DIN 46228 pt 1, min.       | 0.2 mm <sup>2</sup>      | w. wire end ferrule, DIN 46228 pt 1, max.       | 1.5 mm <sup>2</sup> |
| Plug gauge acc. to EN 60999 a x b; Ø            | 2.4 mm x 1.5 mm ; 2.4 mm |   |                     |


**OMNIMATE Signal - series BC/SC 3.81  
SCZ 3.81/12/180F SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com


**Technical data**
**Rated data acc. to IEC**

|   |                        |   |                  |
|---|------------------------|---|------------------|
| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. no. of poles (Tu=20°C)                            | 17.5 A           |
| Rated current, max. no. of poles (Tu=20°C)                                | 17.1 A                 | Rated current, min. no. of poles (Tu=40°C)                            | 17.5 A           |
| Rated current, max. no. of poles (Tu=40°C)                                | 15.2 A                 | Rated voltage for surge voltage class / pollution degree II/2         | 320 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V            |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 76 A |

**Rated data acc. to CSA**

|                               |   |                               |                |
|-------------------------------|---|-------------------------------|----------------|
| Institute (CSA)               |  | Certificate No. (CSA)         | 200039-1121690 |
| Rated voltage (Use group B)   | 300 V   | Rated voltage (Use group C)   | 50 V           |
| Rated current (use group B)   | 11 A  | Rated current (use group C)   | 11 A           |
| Wire cross-section, AWG, min. | AWG 28  | Wire cross-section, AWG, max. | AWG 16         |
| Reference to approval values  | Specifications are maximum values, details - see approval certificate.            |                               |                |

**Rated data acc. to UL 1059**

|                               |   |                               |        |
|-------------------------------|---|-------------------------------|--------|
| Institute (cURus)             |  | Certificate No. (cURus)       | E60693 |
| Rated voltage (use group B)   | 300 V   | Rated voltage (use group D)   | 300 V  |
| Rated current (use group B)   | 10 A  | Rated current (use group D)   | 10 A   |
| Wire cross-section, AWG, min. | AWG 28  | Wire cross-section, AWG, max. | AWG 16 |
| Reference to approval values  | Specifications are maximum values, details - see approval certificate.              |                               |        |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 4.0   | EC002637    | ETIM 5.0   | EC002637    |
| ETIM 6.0   | EC002637    | UNSPSC     | 30-21-18-01 |
| eClass 6.2 | 27-26-07-04 | eClass 7.1 | 27-44-04-02 |
| eClass 8.1 | 27-44-04-02 | eClass 9.0 | 27-44-04-02 |
| eClass 9.1 | 27-44-04-02 |            |             |

**Data sheet**

**OMNIMATE Signal - series BC/SC 3.81  
SCZ 3.81/12/180F SN OR BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

**Notes**

|                |  |
|----------------|--|
| Notes          | <ul style="list-style-type: none"> <li>• Additional colours on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> </ul> |
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.   |

**Approvals**

|           |   |
|-----------|---|
| Approvals |  |
| ROHS      | Conform   |

**Downloads**


|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>  |
| Brochure/Catalogue                          | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">CAT 2 PORTFOLIOGUIDE EN</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FLIndustr.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL_BASE_STATION EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a> |

**OMNIMATE Signal - series BC/SC 3.81  
SCZ 3.81/12/180F SN OR BX**


**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**


**Dimensional drawing**



**Graph**



**Graph**



**Graph**

