



Precision ESD Safe Dissipative Screwdrivers

Wiha Precision ESD Static Dissipative Screwdrivers meet the requirements for tools used in static sensitive areas



Rotating cap

For precise turning & control with fingertip

Molded Precision handle

Impact resistant dissipative material

Tapered handle

allows rapid rotation

Blade

CVM steel, hardened, hard chrome finish

Tip

Precision ground for exact fit, Wiha Chromtop finish

ESD Standard IEC 61340-5-1

Surface resistance of handles is $10^6 - 10^9$ Ohms



27390 Set 7 Pcs. Slotted & Phillips Precision ESD Safe Dissipative Handle

Blade high alloy CVM steel, hardened, hard chrome. Handle manufactured from impact resistant, dissipative material.

ESD standard IEC 61340-5-1

Item No.	Slotted:	lbs.
27390	1.5, 2.0, 2.5, 3.5mm	.30
	Phillips:	
	#00, 0, 1	



272 Slotted Screwdriver, With Precision ESD Safe Dissipative Handle

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1.

Item No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
27208	.8	1/32	40	1.6	0.16	120	4.7	.02 10
27210	1.0	.039	40	1.6	0.18	120	4.7	.02 10
27212	1.2	3/64	40	1.6	0.20	120	4.7	.02 10
27215	1.5	1/16	40	1.6	0.25	120	4.7	.02 10
27218	1.8	5/64	40	1.6	0.30	120	4.7	.02 10
27220	2.0	5/64	40	1.6	0.40	120	4.7	.02 10
27222	2.0	5/64	75	3.0	0.40	155	6.1	.03 10
27223	2.0	5/64	100	3.9	0.40	180	7.1	.03 10
27224	2.0	5/64	150	5.9	0.40	260	10.2	.04 10
27225	2.5	3/32	50	2.0	0.40	145	5.7	.04 10
27227	2.5	3/32	100	3.9	0.40	195	7.7	.04 10
27228	2.5	3/32	150	5.9	0.40	245	9.6	.04 10
27230	3.0	1/8	50	2.0	0.50	145	5.7	.04 10
27232	3.0	1/8	100	3.9	0.50	210	8.3	.04 10
27234	3.0	1/8	150	5.9	0.50	260	10.2	.05 10
27235	3.5	9/64	60	2.4	0.60	170	6.7	.06 10
27237	3.5	9/64	100	3.9	0.60	210	8.3	.06 10
27238	3.5	9/64	150	5.9	0.60	260	10.2	.06 10
27240	4.0	5/32	60	2.4	0.80	170	6.7	.06 10
27242	4.0	5/32	100	3.9	0.80	210	8.3	.06 10
27243	4.0	5/32	150	5.9	0.80	260	10.2	.07 10

*Metric dimensions actual - Inch dimensions approximate



27290 Set 8 Pcs. Slotted Precision ESD Safe Dissipative Handle

Blade CVM steel, hardened, hard chrome. Handle impact resistant, dissipative material. In storage pouch. ESD standard IEC 61340-5-1

Item No.	Slotted:	lbs.
27290	.8, 1.0, 1.2, 1.5, 2.0, 2.5, 3.0, 3.5mm	.54



273 Phillips Screwdriver, With Precision ESD Safe Dissipative Handle

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
27302	000	40	1.6	2.0	.08	120	4.7	.02	10
27305	00	40	1.6	2.0	.08	120	4.7	.02	10
27307	00	75	3.0	2.0	.08	155	6.1	.02	10
27310	0	50	2.0	3.0	.12	145	5.7	.04	10
27312	0	75	3.0	3.0	.12	170	6.7	.04	10
27314	0	100	3.9	3.0	.12	195	7.6	.05	10
27316	0	150	5.9	3.0	.12	245	9.6	.06	10
27320	1	60	2.3	4.0	.16	170	6.7	.06	10
27322	1	75	3.0	4.0	.16	155	6.1	.06	10
27324	1	100	3.9	4.0	.16	210	8.2	.06	10
27326	1	150	5.9	4.0	.16	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate



27399 Set 8 Pcs. Slotted & Phillips Precision ESD Safe Dissipative Handle

Blade high alloy CVM steel, hardened, hard chromed. Handle manufactured from impact resistant, dissipative material. Storage pouch. ESD standard IEC 61340-5-1.

Item No.	Slotted:	lbs.
27399	1.5, 2.0, 2.5, 3.0mm	.50
	Phillips:	
	#000, 00, 0, 1	



27393 Set 7 Pcs. Extra Long Slotted/Phillips Precision ESD Safe Dissipative Handle

Blade CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material. ESD standard IEC 61340-5-1

Item No.	Slotted:	lbs.
27393	2.0, 2.5, 3.0, 3.5, 4.0mm	.50
	Phillips:	
	#0, 1	