

**A-series  
A4C 4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

|            |   |
|------------|---|
| Type       | A4C 4   |
| Order No.  | <a href="#">2051500000</a>  |
| Version    | Feed-through terminal, PUSH IN, 4 mm <sup>2</sup> , 800 V, 32 A, Dark Beige |
| GTIN (EAN) | 4050118411621   |
| Qty.       | 50 pc(s).   |

**A-series  
A4C 4**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

|                          |         |                 |            |
|--------------------------|---------|-----------------|------------|
| Width                    | 6.1 mm  | Width (inches)  | 0.24 inch  |
| Height                   | 87.5 mm | Height (inches) | 3.445 inch |
| Depth                    | 39.5 mm | Depth (inches)  | 1.555 inch |
| Depth including DIN rail | 40.5 mm | Net weight      | 15.06 g    |

**Temperatures**

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |
|----------------------------------|--------|----------------------------------|--------|

**Material data**

|                                |        |                           |            |
|--------------------------------|--------|---------------------------|------------|
| Material                       | Wemid  | Colour                    | Dark Beige |
| Colour of operational elements | Orange | UL 94 flammability rating | V-0        |

**Rating data IECEx/ATEX**

|                                |                   |                                 |                   |
|--------------------------------|-------------------|---------------------------------|-------------------|
| Certificate No. (ATEX)         | TUEV16ATEX7909U   | Certificate No. (IECEX)         | IECEXTUR16.0036U  |
| Max. voltage (ATEX)            | 550 V             | Current (ATEX)                  | 28 A              |
| Wire cross section max. (ATEX) | 4 mm <sup>2</sup> | Max. voltage (IECEX)            | 550 V             |
| Current (IECEX)                | 28 A              | Wire cross section max. (IECEX) | 4 mm <sup>2</sup> |

**System specifications**

|                               |       |                                  |    |
|-------------------------------|-------|----------------------------------|----|
| End cover plate required      | Yes   | Number of potentials             | 1  |
| Number of levels              | 1     | No. of clamping points per level | 4  |
| Number of potentials per tier | 1     | PE connection                    | No |
| Mounting rail                 | TS 35 | N-function                       | No |
| PE function                   | No    | PEN function                     | No |

**Additional technical data**

|                     |               |                   |         |
|---------------------|---------------|-------------------|---------|
| Installation advice | Mounting rail | Open sides        | right   |
| Snap-on             | No            | Type of fixing    | Snap-on |
| Type of mounting    | TS 35         | With snap-in pegs | No      |

**CSA rating data**

|                               |                 |                               |        |
|-------------------------------|-----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-70089609 | Current size B (CSA)          | 30 A   |
| Current size C (CSA)          | 30 A            | Current size D (CSA)          | 5 A    |
| Voltage size B (CSA)          | 600 V           | Voltage size C (CSA)          | 600 V  |
| Voltage size D (CSA)          | 600 V           | Wire cross section max. (CSA) | 10 AWG |
| Wire cross section min. (CSA) | 26 AWG          |                               |        |

**A-series  
A4C 4**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Conductors for clamping (rated connection)**

|   |                     |   |                     |
|---|---------------------|---|---------------------|
| Blade size  | 0.6 x 3.5 mm        | Clamping range, max.  | 4 mm <sup>2</sup>   |
| Clamping range, min.  | 0.5 mm <sup>2</sup> | Connection cross-section, stranded, max.  | 4 mm <sup>2</sup>   |
| Connection cross-section, stranded, min.  | 0.5 mm <sup>2</sup> | Connection direction  | top                 |
| Gauge to IEC 60947-1  | A4                  | Number of connections   | 4                   |
| Stripping length  | 12 mm               | Twin wire-end ferrules, max.  | 1.5 mm <sup>2</sup> |
| Twin wire-end ferrules, min.  | 0.5 mm <sup>2</sup> | Type of connection  | PUSH IN             |
| Wire connection cross section AWG, max.   | AWG 12              | Wire connection cross section AWG, min.   | AWG 26              |
| Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>   | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm <sup>2</sup>   |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm <sup>2</sup>   |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup> | Wire connection cross-section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, solid core, max.   | 4 mm <sup>2</sup>   | Wire connection cross-section, solid core, min.   | 0.5 mm <sup>2</sup> |

**Rating data**

|                                 |                   |  |       |
|---------------------------------|-------------------|--|-------|
| Rated cross-section             | 4 mm <sup>2</sup> | Rated voltage                                | 800 V |
| Rated current                   | 32 A              | Current at maximum wires                     | 32 A  |
| Standards                       | IEC 60947-7-1     | Volume resistance according to IEC 60947-7-x | 1 mΩ  |
| Rated impulse withstand voltage | 8 kV              | Pollution severity                           | 3     |
| Surge voltage category          | III               |  |       |

**UL rating data**

|  |        |  |        |
|--|--------|--|--------|
| Certificate No. (cURus)                    | E60693 | Conductor size Factory wiring max. (cURus) | 10 AWG |
| Conductor size Factory wiring min. (cURus) | 28 AWG | Conductor size Field wiring max. (cURus)   | 10 AWG |
| Conductor size Field wiring min. (cURus)   | 28 AWG | Current size B (cURus)                     | 30 A   |
| Current size C (cURus)                     | 30 A   | Current size D (cURus)                     | 5 A    |
| Voltage size B (cURus)                     | 600 V  | Voltage size C (cURus)                     | 600 V  |
| Voltage size D (cURus)                     | 600 V  |  |        |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC000897    | ETIM 6.0   | EC000897    |
| eClass 6.2 | 27-14-11-20 | eClass 7.1 | 27-14-11-20 |
| eClass 8.1 | 27-14-11-20 | eClass 9.0 | 27-14-11-20 |
| eClass 9.1 | 27-14-11-20 |            |             |

**Product information**

|                                 |   |
|---------------------------------|---|
| Descriptive text technical data | Approval in progress                        |
| Descriptive text accessories    | All MultiMark variants (MM) = strip markers |

**Data sheet****A-series  
A4C 4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data****Approvals**

Approvals

**Downloads**Approval/Certificate/Document of  
Conformity

[CFAT\\_A4C\\_4.pdf](#)  
[CFAT\\_A4C\\_4.pdf](#)  
[IECEX\\_TUR\\_16.0036U\\_2.pdf](#)  
[TÜV 16 ATEX 7909 U.pdf](#)  
[DE\\_PT0101\\_20160614\\_065\\_ISSUE01.pdf](#)

Brochure/Catalogue

[CAT 1 TERM 16/17 EN](#)

Engineering Data

[EPLAN, WSCAD, Zuken E3.S](#)

User Documentation

[NTI\\_A4C 4.pdf](#)

**Safety note**

Safety notice

[Safety Information](#)

**Data sheet**

**A-series**  
**A4C 4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

