



Technical Data

Rated power	90 W
Maximum power	130 W
Nominal impedance Z	8 Ohm
Frequency response	fu–6000 Hz
(fu: Lower cut-off frequency depending on cabinet)	.
Mean sound pressure level	90 dB (1 W/1 m)
Excursion limit	+/-10 mm
Resonance frequency fs	45 Hz
Magnetic induction	1.0 T
Magnetic flux	660 μWb
Height of front pole-plate	6 mm
Voice coil diameter	35 mm
Height of winding	12 mm
Cutout diameter	236 mm
Net weight	1.5 kg
D.C. resistance Rdc	6.8 Ohm
Mechanical Q factor Qms	3.57
Electrical Q factor Qes	1.00
Total Q factor Qts	0.78
Equivalent volume Vas	135 l
Effective piston area Sd	360 cm ²
Dynamically moved mass Mms	27 g
Force factor Bxl	6.4 Tm
Inductance of the voice coil L	1.1 mH



W 250
18.01.01