

# Safety Data Sheet



## 1: Product and Company Identification

**Product Name** Flux-cored solder, Tin/Lead alloy and Solders

**Supplier** Premier Farnell plc  
150 Armley Road  
Leeds  
LS12 2QQ  
+44 (0) 870 129 8608

**Emergency Telephone Numbers** +44 1865 407333

## 2: Ingredients and Hazards

**Chemical Characteristics** : Tin/Lead alloy

**Hazardous Material Classification and Figure** : Contains Lead - Harmful  
Contains Rosin - Irritant

Hazardous Ingredients Name	WT%	C.A.S. Number	Organic Standard
Tin / SN	60-64(see product marking)	7440-31-5	Not Applicable
Lead / PB	36-40(see product marking)	7439-92-1	Not Applicable
Rosin	2.0~3.0	8050/9/7	Not Applicable

## 3: Health Hazard Data

**The most hazard and effects** : Inhalation, eyes contact and ingestion during use of the product.

**GHS**



Hazard Warning

**Inhalation**

: When welding and the temperature can be up to 500°C, fume could be generated to cause anemia, constipation, abdominal pain . Over inhalation could be harmful to such systems as blood, nerv, fertile, digestion and urinary, In addition, the lead fume could be harmful to infantile nerve system of pregnant mother.

**Skin contact**

: The melt and high-temperature tin-lead alloy could cause skin scalding.

**Eye contact**

: Fume could be irritant or allergic to eyes.

**Ingestion**

: It could cause vomiting; periodic ingestion could cause nerve system paralysis of arm and medial malleolus.

**Symptom of hazard**

: Irritation of eyes, headache, skin allergy.

## 4: Emergency First Aid

**Different routes of entry** : Eyes, skin contact, inhalation & ingestion



# Safety Data Sheet



**Inhalation** : Remove person from exposure and restore breathing fresh air first, then get medical treatment.  
**Skin contact** : Wash with soap water, use cold water to soak the scalded skin and see doctor for treatment, if necessary.  
**Eye contact** : Flush eyes with large amount of water and get medical attention.  
**Ingestion** : Get medical attention.

## 5: Fire and Explosion Hazard Data

**Extinguishing Media** : CO<sub>2</sub>, Chemical powder, Bubble type Extinguisher, Water  
**The hazard when extinguishing** : Spraying melt alloy when it is being pouring water could cause persons to be scalded.  
**Special firefighting procedures** : None recommended  
**Protective measures for firefighting man** : Protective cloths and breath device are required to wear.

## 6: Procedures if Material is Spilled or Released

**Precautions for person** : Recycle when the temperature of the spilled materials becomes cool and returns normal, but be careful to treat in order to avoid scalding.  
**Precautions for environment** : Spilled materials must be recycled.  
**Steps to be taken if material is spilled or released** : Scrape off and recycle when spilled materials are cooling down.

## 7: Precautions to be taken in handling and storage

**Handling** : Working temperature shall not exceed 500°C in which persons shall wear protective equipment to avoid inhaling gas, powdery dust.  
**Storage** : store in waterproof and non-polluted area. Put warning label and check regularly.

## 8: Protective measures against exposure

**Material engineering control** : Provide adequate exhaust ventilation (general and/or local) necessary to meet exposure requirements. Control exposure concentration as low at allowable level.

Control Parameters		
Average allowable concentration when 8 hours running TWA	Average allowable concentration when Short-time running STEL	Average concentration allowed CEILING
Sn : 2.0mg/m <sup>3</sup> ; Pb : 0.05mg/m <sup>3</sup>	Sn : 2mg/m <sup>3</sup> ; Pb : 0.15mg/m <sup>3</sup>	Sn : 58.2mg/m <sup>3</sup> ; Pb : 38.8mg/m <sup>3</sup>

### Protective Measures

**Respiratory Protection** : Wearing respirator is required.  
**Protective gloves** : Required.  
**Eye protection** : Use goggles or face shield  
**Other protective clothing/shoes and equipment** : Recommended.  
**Hygienic work practices** : Wash hands and face after handling chemicals. Smoking or eating is not allowed when working.



# Safety Data Sheet



## 9: Physical and Chemical Data

Material state	: Solid
Color	: Silver-gray
pH	: Not applicable
Decomposition temperature	: None
Auto-ignition temperature	: Not applicable
Vapor pressure	: Not applicable
Specific gravity water	: 1
Appearance	: wire1, strap, bar
Odor	: None
Boiling point	: -
Melting point	: 183°C
Flash Point	: Not applicable
Exposure limit	: Not determined
Vapor density	: Not applicable
Solubility	: None in water

## 10: Stability and Reactivity

Stability	: Stable under all conditions
Probably hazard effect under special condition	: None known
Condition to avoid	: Heat, Flame, Wet and soaking
Materials to avoid	: Strong acids, strong oxidizing materials
Hazardous decomposition products	: Metal powdery dust and gas

## 11: Toxicological Properties

Level of Toxicity	
Acute effect	: Possibly cause irritation to eyes, nose, throat and skin.
Local effect	: None known.
Sensitivity	: None known
Effects of chronic exposure	: Patients with skin or respiratory problems are likely to be harmful.
Special effects	: None known.

## 12: Ecological Data

Probable effect to environment :

1. Soil dispersal
2. Water dispersal
3. Air dispersal

## 13: Waste Disposal

**Waste disposal method** : Solder metal can be recycled by reclamation.



# Safety Data Sheet



## 14: Delivery Information

**International delivery regulation** : LATA-Dangerous Goods Regulation, Not restricted

**UN code** : Not regulated

**Domestic delivery regulation** : Road traffic Safety Regulation Item 84  
Vessel regulations on dangerous goods  
Railroad regulations on dangerous goods

**Special delivery method and precaution** : None known

## 15: Law and Regulation

**Conform to regulation** : 1. Labor Safety & Sanitary Device Regulation  
2. Standards for the density of hazardous materials for labor working environment  
3. Identification rules for hazardous and harmful materials  
4. Standards for waste disposal treatment and facility requirement  
5. Road traffic safety rules

<b>Part Number</b>
--------------------

21-1047
---------

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.

