



Model No. 406GRN

Green dielectric Zenex™ thermoplastic safety padlock, 38mm wide with 38mm nylon shackle

Best Used For:



Electrical Lockout



Safety Lockout/Tagout

Overview & Features

Product Features

- 406 dielectric thermoplastic safety padlock
- Plastic shackle helps prevent electrocution and arc flashing, also prevents electrical current from shackle to key
- All components are non-sparking and non-magnetic - plastic, copper, brass
- 38mm wide, 44mm tall, thermoplastic body, with 38mm shackle length
- Designed exclusively for lockout tagout applications
- Durable, lightweight, non-conductive thermoplastic lock body
- Compliance with "One Employee, One Lock, One Key" best practice
- Key retaining - ensures that padlock is not left unlocked
- Keyed different, 6-pin tumbler with over 40,000 available key changes cylinder
- Commercial Packaging, Shelf Pack Qty 6, Master Carton Qty 36

Certifications




Product Details

The Master Lock No. 406GRN Dielectric Thermoplastic Safety Padlock features a 38mm wide Zenex™ Thermoplastic green body and a 38mm tall, 6mm diameter plastic shackle to help prevent electrocution and arc flashing and to prevent electrical current from shackle to key. All components are non-sparking and non-magnetic. Designed exclusively for Lockout/Tagout applications, the durable, lightweight material is easy to carry and padlock has key retaining cylinder to ensure the padlock is not left unlocked.

Product Specifications

Product Number	406GRN
Body Width	38mm
Shackle Dimensions	A: 6mm B: 38mm C: 20mm
Colour	Green
Description	Keyed Different, Commercial Boxed Packaging
Shelf Pack Qty	6
Master Carton Qty	36



Master Lock Europe S.A.S.

10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu