



Specification
VT4 Voltage Tester



Electrical

Maximum voltage: 1000V AC rms

Voltage sensitivity ranges:

12 to 1000V AC rms

50 to 1000V AC rms (default range)

Frequency range: 50 to 400Hz

Environmental

Temperature & Humidity (Operating & Storage):

0°C to 40°C ≤ 80% R.H.

Altitude: up to 2000m

Pollution degree 2

General

Power: 2 x 1.5V, AAA alkaline batteries (IEC LR03, NEDA 24A)

Battery consumption: 80mA approx.

Dimensions: 155(L) x 23(W) x 25(D) mm

Weight: 55g approx.

Includes: 2 x 1.5V AAA batteries, instructions

Safety

Conforms to BS EN61010-1:2010 CAT IV 1000 V

Class II, Double insulation

IP rating: IP64 to BSEN 60529

EMC

Conforms to BS EN61326-1

Check out what else you can get from Martindale:

- 18th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited
Metrohm House, Imperial Park, Imperial Way,
Watford, Hertfordshire, WD24 4PP, UK
Tel: +44(0)1923 441717 Fax: +44 (0)1923 446900
E-mail: sales@martindale-electric.co.uk
Website: www.martindale-electric.co.uk

© 2014 Martindale Electric Company Ltd.
Registered in England No. 3387451. E. & O.E.
LITVT4 Document Rev2