

**ModuPlug
HDC MHP 100 FC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Type	HDC MHP 100 FC
Order No.	1429080000
Version	Module
GTIN (EAN)	4050118233513
Qty.	1 pc(s).

**ModuPlug
HDC MHP 100 FC**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Net weight 14.4 g

Temperatures

Limit temperature -40 °C ... 125 °C

General data

Insulation resistance	10 ¹² Ω	Material	Polycarbonate, glass fibre reinforced
No. of poles	2	Plugging cycles	≥ 500
Pollution severity	3	Rated current (DIN EN 61984)	100 A
Rated impulse voltage (DIN EN 61984)	8 kV	Rated voltage (DIN EN 61984)	1,000 V
Rated voltage according to UL/CSA	600 V	Required plug-in slots	1.5
Series	ModuPlug	Surge voltage category	III
Type	Female	UL 94 flammability rating	V-0

PE connection data

Connection type PE Screw connection via module frame

Version

Conductor cross-section, max.	35 mm ²	Conductor cross-section, min.	10 mm ²
Type of connection	Crimp connection		

Classifications

ETIM 6.0	EC002312	eClass 6.2	27-14-34-19
eClass 9.1	27-44-02-18		

Approvals

Approvals




Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN FL FIELDWIRING EN
Engineering Data	EPLAN


**ModuPlug
HDC MHP 100 FC**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com


Drawings




**HDC-MHP100-Module im IP65-Gehäuse,
Leiter H07V-K10:**



**HDC-MHP100-Module im IP65-Gehäuse,
Leiter H07V-K35:**



**HDC-MHP100-modules in the IP65-housing,
Conductor H07V-K10:**



**HDC-MHP100-modules in the IP65-housing,
Conductor H07V-K35:**

