

## Harrier PIR C/W Wall/Ceiling Bracket

Features: Dual Element Pyro Sensor, S.M.D Technology, 12 Meter, 110° Convex Honey Comb, Hemispherical, Fresnel Lens, Thermal Optic Protection Cavity, Excellent False Alarm Suppression, Walk Test LED High RFI & EMI Immunity, Pulse Count 1, 2 & 4 Jumper selectable, Grade I.



### Product Specification

#### General Specifications

<b>Type</b>	Dual element pyro sensor
<b>Digital pulse count</b>	1, 2 & 4 jumper selectable

#### Operation Specifications

<b>Alarm period</b>	Greater than 2 seconds
<b>Mounting Height</b>	2m
<b>Range</b>	12m 110° volumetric
<b>Detection Speed</b>	0.3—3ms

#### European Standards:

Electro-magnetic Compatibility (EMC) 89/336/EEC  
(Amended by 92/31/EEC and 93/68EEC) RoHS

#### Electrical Specification

<b>Operating voltage</b>	9-16Vdc
<b>Operating current</b>	8mA
<b>Alarm contacts</b>	Normally closed dry contacts (0.5A/24V)
<b>Tamper contacts</b>	Normally closed dry contacts (0.5A/24V) with 15Ω resistor in series
<b>Storage temperature</b>	-10 to + 50°C

#### Technical Specification

<b>Plastic housing material</b>	ABS
<b>Dimensions</b>	100mm X 65mm X 45mm
<b>Weight</b>	100g

#### Order Code

**LY15-007-32**