


FEELER GAUGES

THICKNESS GAUGES

- Hardened and tempered high quality steel thickness blades.

W129C



electrode adjuster



W131C 3" steel rule.

STANDARD FEELER GAUGES

- Check for accurate clearance on ignition points, valve lash, etc.
- SAE and Metric sizes.

**W80527/
W80528**




W80526



non magnetic brass blades.

W80541



12 x 1/2"

W80526

W80525
1-1/2 x 1/4"

| Item # | IP | MP | PKG | Sizes |
|---------------------------------|----|-----|-----|--|
| W125C 32 Blades | 6 | 192 | CRD | Features a .010" brass blade for transistorized ignitions. SAE: .0015, .002, .0025, .003, .004, .005, .006, .007, .008, .009, .010, .011, .012, .013, .014, .015, .016, .017, .018, .019, .020, .021, .022, .023, .024, .025, .026, .028, .030, .032, .035". Metric: .04, .05, .06, .08, .10, .13, .15, .18, .20, .23, .25, .28, .30, .33, .35, .38, .40, .43, .45, .48, .50, .53, .55, .58, .60, .63, .65, .70, .75, .80, .88 mm. |
| W129C 15 Blades | 6 | 192 | CRD | Features 9 straight 2" thickness blades, 6 flat 1" spark plug blades, 2" steel rule and electrode adjuster. Straight Blade SAE: .002, .003, .004, .006, .008, .010, .015, .017, .018, .019, .020 and .025". Metric: .05, .08, .10, .15, .20, .25, .38, .432, .457, .483, .50 and .63 mm. Flat Blade SAE: .020, .025, .028, .030, .035 and .040". Metric: .50, .64, .70, .75, .88 and 1.02 mm |
| W131C 15 Blades | 6 | 192 | CRD | SAE: .002, .003, .004, .005, .006, .008, .011, .012, .013, .014, .016, .018, .020, .022 and .025". Metric: .05, .08, .10, .13, .15, .20, .28, .30, .33, .35, .40, .45, .50, .55 and .63 mm. |
| W80527 25 Blades | 12 | 192 | CRD | Metric: .04, .05, .06, .07, .08, .09, .10, .15, .20, .25, .30, .35, .40, .45, .50, .55, .60, .65, .70, .75, .80, .85, .90, .95 and 1.00 mm |
| W80528 26 Blades | 12 | 192 | CRD | SAE: .0015, .002, .0025, .003, .004, .005, .006, .007, .008, .009, .010, .011, .012, .013, .014, .015, .016, .017, .018, .019, .020, .021, .022, .023, .024 and .025". Metric: .038, .051, .064, .076, .102, .127, .152, .178, .203, .229, .254, .279, .305, .330, .356, .381, .406, .432, .457, .483, .508, .533, .559, .584, .610 and .635 mm |
| W80526 6 Blades | 12 | 192 | CRD | SAE: .006, .008, .010, .012, .014 and .016". Metric: .152, .203, .254, .305, .356 and .406 mm |
| W80525 17 Blades | 12 | 192 | CRD | SAE: .010, .012, .013, .015, .016, .017, .018, .019, .020, .022, .024, .025, .026, .028, .030, .032 and .035" |
| W84601 16 Blades | 12 | 192 | CRD | SAE: .011, .012, .013, .014, .015, .016, .017, .018, .019, .020, .022, .024, .025, .028, .030 and .032". Metric: .279, .305, .330, .356, .381, .408, .432, .457, .483, .508, .559, .610, .635, .711, .762 and .813 mm |
| W80541 20 Blades | 6 | 36 | CRD | SAE: .002, .004, .006, .008, .010, .012, .014, .016, .018, .020, .022, .024, .026, .028, .030, .032, .034, .036, .038, .040" |

See Engine section for tappet gauges

COMBINATION TUNE-UP GAUGE

- Features 12 straight steel blades, 6 straight brass blades, 6 wire test loops, and electrode adjuster.



W80529

| Item # | IP | MP | PKG | Sizes |
|---|----|-----|-----|---|
| W80529 18 Blades 6 Loops | 12 | 192 | CRD | Steel Blade SAE: .010, .012, .015, .016, .017, .018, .019, .020, .022, .024, .025 and .026". Metric: .254, .305, .381, .406, .432, .457, .483, .508, .559, .610, .635 and .660 mm. Magnetic Blade SAE: .006, .008, .010, .012, .014 and .016". Metric: .152, .203, .254, .305, .356 and .406 mm. Wire Test Loop SAE: .025, .030, .034, .035, .040 and .045" |