

DHP481Z

Chuck Capacity	1.5 - 13 mm
Blows per Minute (Hi) - ipm	0 - 31,500 ipm
Blows per Minute (Lo) - ipm	0 - 8,250 ipm
No Load Speed (Hi)	0 - 2100 rpm
No Load Speed (Lo)	0 - 550 rpm
Voltage	18 v
Max. in wood	76 mm
Max. in masonry	16 mm
Max. in steel	13 mm
Torque Settings	21 + drill
Battery Type	Lithium-ion
Vibration K factor	1.5 m/sec ²
Body only machine	1
Max. Fastening Torque (Soft Joint)	60 Nm
Max. Fastening Torque (Hard Joint)	115 Nm
Vibration: Impact drilling into concrete	6.5 m/sec ²
Vibration: Drilling into metal	2.5 m/sec ²
Weight (with batteries)	2.7 - 3.0 kg



- Forward/reverse rotation
- Single sleeve keyless chuck allows for easy bit installation/removal by one hand.
- Electric brake
- Twin LED job light with afterglow.
- 2 mechanical gears.
- Battery fuel gauge
- Variable speed control by trigger
- Best possible ergonomic handle for drill-driver applications.
- Compact overall length.