



Type N F/F In/Out RF Coaxial Surge Protector 100MHz - 512MHz
DC Block 750W IP67 20kA Filter Bracket Toward Body

RF Surge Protectors Technical Data Sheet

LCSP1033

Environmental Specifications

Temperature

Operating Range

-50 to 85 deg C

Ingress Protection (IP) Rating

IP 67

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Our portfolio includes cable assemblies, connectors, adapters and custom products, as well as their wireless product line which includes antennas, RF amplifiers, coaxial lightning and surge protectors, and NEMA rated enclosures.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Type N F/F In/Out RF Coaxial Surge Protector 100MHz - 512MHz DC Block 750W IP67 20kA Filter Bracket Toward Body LCSP1033](#)

URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume any liability arising out of the use of any part or documentation.

