

Product information

TWIN 18V ROTARY HAMMER SDS+ LXT



Satisfying the professional's needs

DHR263ZJ

| | |
|--------------------------------|-------------------------|
| Battery Type | Lithium-ion |
| Body only machine | 1 |
| Voltage | 36 (18V x2) v |
| Max in concrete | 26 mm |
| Max. in steel | 13 mm |
| Max. in wood | 32 mm |
| Impacts per Minute | 0-4800 ipm |
| No Load Speed | 0-1,200 rpm |
| Vibration K factor | 1.5 m/sec ² |
| Vibration: Hammer Drilling | 14.5 m/sec ² |
| Vibration: Chiselling | 14 m/sec ² |
| Vibration: Drilling into metal | 3 m/sec ² |
| Net weight | 4.1 - 5.1 kg |



STANDARD EQUIPMENT: 821552-6 MAKIPAC CONNECTOR CASE (TYPE 4), 837988-9 INNER TRAY, Depth stop, Side handle, Bit grease

- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Compact design that maintains the same easy handling and high manoeuvrability as the BHR262.
- LED Job light with pre-glow and afterglow functions
- 3 mode operation • Rotation + Hammering • Hammering only • Rotation only
- When different capacity batteries are used together, (for example 3.0Ah BL1830 and 4.0Ah BL1840, or fully charged BL1830 and 70% charged BL1830), the machine stops when the battery with less capacity gets empty.
- One touch slide chuck for SDS-plus bit.
- Ergonomic soft grip
- Battery capacity warning lamp.
- 40 different bit-angle settings.

Details correct as of: 2-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com