


# Rocker Switches

## Non-Illuminated, Round



### Specifications

Actuator	: Non-Illuminated, Round
Terminal	: Quick Connect Tab
Ambient Temperature	: Terminal Side: -20°C to +85°C Actuating Side: -20°C to +55°C
Atmospheric Humidity	: 85% Max.
Actuating Force	: 3 ~ 6N
Storage Temperature	: -30°C to +80°C Max
Temperature Rise	: 30°C Max. @ Terminal
Solder Ability	: 350°C Max., 3s
Safety Approval	: UL, VDE

### Electrical Specifications

Parameter	UL	VDE/ENEC10
Electrical Rating	10A, 250V AC/15A, 125V AC	10A (4A), 250V AC
Electrical Life Endurance	10,000 times	
Contact Resistance	< 20mΩ	
Insulation Resistance	> 1,000MΩ	
Dielectric Strength	> 1,500V/minute	
Temperature Rise	30° C	
Push forces for TABS	≥6kg	
Pull forces for TABS	≥10kg	
Operating Force	550g ±100g; RC2: 400g ±100g	
Force for Button	≥9kg	
Horizontal direction forces for TABS	≥2kg	

### Material Specifications

Housing	: Polyamide 6.6, Black
Rocker	: Polyamide 6.6 & Polycarbonate, Black
Contacts	: Silver Alloy
Terminal	: Copper or Brass, Silver Plated
Spring	: SWC (Chromated Steel Wire)
Movable Arm	: Brass, Silver Plated

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)



# Rocker Switches


## Non-Illuminated, Round



### Switch Function

Poles & Throw	Rocker Position ( ): Momentary			Actuator Type	Part Number
	Left	Center	Right		
SPST	On	None	Off	Round - No Marking	MCRC-1-5-KK-E-T00B
SPST	On	None	Off	Round - O/I Marking	MCRC-1-5-KK-F-T00B
SPDT	On	None	On	Round - No Marking	MCRC-2-5-KK-E-T00B

### Dimension



Dimensions : Millimetres (Inches)

### Part Number Table

Description	Part Number
Rocker Switch, Non-Illuminated, Round, SPST, On-None-Off, QC, Black	MCRC-1-5-KK-E-T00B
Rocker Switch, Non-Illuminated, Round, O/I Marking, SPST, On-None-Off, QC, Black	MCRC-1-5-KK-F-T00B
Rocker Switch, Non-Illuminated, Round, SPDT, On-None-On, QC, Black	MCRC-2-5-KK-E-T00B

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com  
 www.farnell.com  
 www.newark.com

