

True RMS AC Flex Clamp Meter



RoHS
Compliant



Features

- Ergonomically Designed One Hand Operation
- 3000 Count Large Scale LCD Display with Backlit
- 3000A AC Current
- Head Cable Length 18" (457mm)
- Auto Ranging
- Data Hold & Max/Min
- 7.5mm Coil Diameter for Tight Space Measurement
- Low Battery Indication
- CAT IV 600V/CAT III 1000V Safety Standard

Specifications

Function	Range	Resolution	Accuracy (% of reading + digits)
AC Current 50~400Hz True RMS	30.00A AC	0.01A	$\pm(3.0\% +8d)$
	300.0A AC	0.1A	$\pm(3.0\% +5d)$
	3000A AC	1A	$\pm(3.0\% +5d)$

Note: Accuracy is given as $\pm(\%$ of reading + counts of least significant digit) at 23°C \pm 5°C, with relative humidity less than 80%RH. The measured conductor is placed in the center of the coil.

Part Number Table

Description	Part Number
True RMS AC Flex Clamp Meter, 3000A, 457mm Cable	72-14435

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

