

PT-E550WSP

Handheld Electrician Labelling Printer



Top Features:

Backlit graphic display

- Easy-to-read text and the ability to preview your label before printing.

Multiple power options

- Supplied with an AC adaptor and a rechargeable Li-ion rechargeable battery. Also works with 6 AA batteries (not supplied)

Lots of built-in contents

- Customise labels using a choice of 9 fonts, 7 frames and 384 symbols

Built-in auto full & half cutter

- Guaranteed to cut strong adhesive tapes
- Perfect for printing multiple/sequentially numbered labels
- With cut/pause to help reduce waste

Wi-Fi enabled

- Print to the device via the network
- Transfer content such as label templates, databases or custom symbols wirelessly from your PC to the PT-E550W
- Establish a P2P connection with your mobile devices (iOS and Android) in the direct mode to create label layouts on your Smartphone

Standard PC style keyboard

- Makes typing efficient.

Convenient labelling

- Handheld design and battery power lets you print labels wherever they are required.

Smart label application keys to save time

- General/Faceplate
- Cable Wrap/Cable Flag/Heat Shrink Tube/¹Self-laminated
- Patch Panel / Punch Down Block
- Serialize / Advanced Serialize

Specialist HSe heat shrink tubes available

- HSe-211 (5.8mm)
- HSe-221 (8.8mm)
- HSe-231 (11.7mm)
- HSe-241 (17.7mm)
- HSe-251 (23.6mm)

General

Carton contents	PT-E550WSP labelling machine 12mm black on white flexible ID tape cassette (8m) 18mm black on white laminated tape cassette (8m) 24mm black on white laminated tape cassette (8m) 24mm black on yellow laminated tape cassette (8m) Li-ion rechargeable battery AC adaptor Wrist strap Documentation USB-mini cable Software CD Carry case
Language support	English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Brazilian Portuguese, Turkish

Dimensions & Weights

Without carton	126(w) x 250(d) x 94(h) 1.05 kg
With carton	393(w) x 334(d) x 126(h) 3.25 kg
Master carton	413(w) x 348(d) x 390(h) 11.04 kg

Built In Features

Keyboard	70 Key Rubber QWERTY/QWERTZ/AZERTY
Dedicated number keypad	Yes
Interfaces	USB, Wi-Fi
Operating system support	Microsoft Windows® Vista, Windows® 7, Windows® 8, Mac OS/X 10.7to 10.9.
Display type	Backlit Graphic Monochrome LCD with label preview capability
Display resolution	16 characters by 3 lines 128 x 64 dots
Printing speed	Up to 30mm/second
Print resolution	180dpi
Maximum print height	18.0mm
Cutter type	Auto Full & Half (with cut/pause feature) (fluorine-coated to cut strong adhesive tapes)
Label length	15mm minimum 999mm maximum
Maximum lines per label	7 (for 24mm wide tape)
Tape margins	Auto Cut: On/Off, Half Cut: On/Off, Chain Printing: On/Off, Special Tape: On/Off
Vertical text printing	Yes
Mirror printing	No
Copies	1 to 99
Automatic numbering	Yes (1 – 99, Normal, Simultaneous, Advanced)

Label Creation

Smart label application keys	General, Faceplate, Cable Wrap, Cable Flag, Heat Shrink Tube, Patch Panel, Punch Down Block
Fonts	14 Helsinki, Brussels, US, Los Angeles, San Diego, Florida, Calgary, Belgium, Atlanta, Adams, Brunei, Sofia, Germany, Letter Gothic
Font styles	9 (excl. Normal) Normal, Bold, Outline, Shadow, Solid, Italic, Italic Bold, Italic Outline, Italic Shadow, Italic Solid
Font sizes	6, 9, 12, 18, 24, 36, 42, 48 point
Symbols	384
Frames	7
Barcodes	9 CODE39, ITF 2/5, EAN13, EAN8, UPC-A, UPC-E, CODABAR, GS1-128 (UCC/EAN128), CODE128

Memory

Max. characters per label	1,500
Label memory locations	99 (or up to 18,297 characters)
Transferred content	6 MB Label templates: up to 99 Custom symbols: up to 99 Databases: up to 99

Supplies

Tape type	TZe, HGe, HSe (Heat Shrink Tube)
Tape widths	3.5, 6, 9, 12, 18 & 24mm
Optional Accessories	
Batteries	BA-E001 Li-ion rechargeable battery AA alkaline/rechargeable batteries (LR6/HR6) x 6
AC adaptor	AD-E001