

MFG Part Number	Newark Part Number	Color	Length
83-12237	24T3636	BLACK	915 +/- 30mm
83-7856	50B5351	BLACK	1830 +/- 50mm
83-7857	92B0628	BLACK	3050 +/- 60mm
83-7858	38C8979	BLACK	4575 +/- 50mm
83-7859	92B0629	BLACK	7620 +/- 80mm
83-7860	92B0630	BLACK	15240 +/- 100mm
83-7861	38C8980	BLACK	22875 +/- 100mm
83-7862	99B1902	BLACK	30500 +/- 100mm

NOTE:

- CABLE: 28AWG(7/0.12TC),UL2919,AL+D+B,[(28AWG*1C+D+AL)*3COAX+28AWG*5PAIR],OD=9.0±0.2mm.BLACK WITH EMBOSS,PVC JACKET.
- LENGTH: L.
- CONNECTORS: HDB15M*2PCS(BLACK INSULATION)(SHELL NICKEL).
CORE: (17.5*28.5*10.7)*2PCS.
SCREW: #4-40Al*4*40.3 BLACK SCREW*4PCS.
NUTS: #4-40 L60*W4.8 NUTS*2PCS PE BAG(06*2.5*5CM).


- MOLD: MOLDING TYPE.
- CONTACTS:

HDB15M	1	6	2	7	3	8	4	14	5	12	10	13	11	15	9	64
HDB15F	1	6	2	7	3	8	4	14	5	12	10	13	11	15	9	64
	RC	RG	BC	BG	GC	GG	PAIR	PAIR	PAIR	PAIR	PAIR	PAIR	PAIR	PAIR	PAIR	SHELL


- Test machine test condition.

- 100% OPEN,SHORT&INTERMITANCE TEST.
- CONDUCTOR RESISTANCE: 3ohms MAX:
- INSULATION RESISTANCE: 5M Min/,10ms:


- ALL MUST BE MEET ON ROHS COMPLIANT.



Printing CTN Color: Blue



Printing PE BAG (COLOR: BLACK)



COMPANY	REVISION	DATE	DISCRIPTION	ITEM NO.	83-12237	NO	B	SCALE	NON	
	REV.A/0	2015.04.14		DRAWN BY					UNIT(mm)	⊕
				DESIGNED BY					DRAWING NO.	
				APPROVAL BY						