



High Performance Schottky Rectifier, 2 x 30 A



| PRIMARY CHARACTERISTICS | | | | | | | | | |
|----------------------------------|-----------------|--|--|--|--|--|--|--|--|
| I _{F(AV)} | 2 x 30 A | | | | | | | | |
| V_{R} | 150 V | | | | | | | | |
| V _F at I _F | 0.72 V | | | | | | | | |
| I _{RM} max. | 20 mA at 125 °C | | | | | | | | |
| T _J max. | 175 °C | | | | | | | | |
| E _{AS} | 0.4 mJ | | | | | | | | |
| Package | 3L TO-220AB | | | | | | | | |
| Circuit configuration | Common cathode | | | | | | | | |

FEATURES

- 175 °C T_J operation
- Low forward voltage drop
- High frequency operation





- Guard ring for enhanced ruggedness and long term reliability
- Designed and qualified according to JEDEC®-JESD 47
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

DESCRIPTION

The VS-60CTQ150... center tap Schottky rectifier series has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 175 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

| MAJOR RATINGS AND CHARACTERISTICS | | | | | | | | |
|-----------------------------------|---|-------------|-------|--|--|--|--|--|
| SYMBOL | CHARACTERISTICS | VALUES | UNITS | | | | | |
| I _{F(AV)} | Rectangular waveform | 60 | Α | | | | | |
| V _{RRM} | | 150 | V | | | | | |
| I _{FSM} | t _p = 5 μs sine | 710 | Α | | | | | |
| V _F | 30 A _{pk} , T _J = 125 °C (typical, per leg) | 0.69 | V | | | | | |
| T_J | Range | -55 to +175 | °C | | | | | |

| VOLTAGE RATINGS | | | | | | | | |
|--------------------------------------|-----------|----------------|-------|--|--|--|--|--|
| PARAMETER | SYMBOL | VS-60CTQ150-M3 | UNITS | | | | | |
| Maximum DC reverse voltage | V_{R} | 150 | V | | | | | |
| Maximum working peak reverse voltage | V_{RWM} | 150 | V | | | | | |

| ABSOLUTE MAXIMUM RATINGS | | | | | | | | |
|---|---|--|--|-------|-----|--|--|--|
| PARAMETER | SYMBOL | TEST CONDI | VALUES | UNITS | | | | |
| Maximum average forward per leg | | 50 % distributed at T = 107 % restaurations | | 30 | | | | |
| current, see fig. 5 per device | I _{F(AV)} 50 % duty cycle at T _C = 137 °C, rectangular waveform | | | | i _ | | | |
| Maximum peak one cycle non-repetitive | | 5 μs sine or 3 μs rect. pulse | Following any rated load condition and | 710 | A | | | |
| surge current per leg, see fig. 7 | I _{FSM} | 10 ms sine or 6 ms rect. pulse | with rated V _{RRM} applied | 270 | | | | |
| Non-repetitive avalanche energy per leg | E _{AS} | T _J = 25 °C, I _{AS} = 0.9 A, L = 1 mH | | 0.4 | mJ | | | |
| Repetitive avalanche current per leg | I _{AR} | Current decaying linearly to zero in 1 μs Frequency limited by T_J maximum $V_A = 1.5 \ x \ V_R$ typical | | 0.9 | Α | | | |




| ELECTRICAL SPECIFICATIONS | | | | | | | | | |
|---|--------------------------------|---|---------------------------------------|--------|-------|----|--|--|--|
| PARAMETER | SYMBOL | TEST CO | TYP | MAX. | UNITS | | | | |
| | | 30 A | T _{.1} = 25 °C | 0.83 | 0.88 | | | | |
| Maximum forward voltage drop per leg | V _{FM} ⁽¹⁾ | 60 A | 1j=25 C | 0.98 | 1.09 | V | | | |
| See fig. 1 | V _{FM} ('') | 30 A | T _{.1} = 125 °C | 0.67 | 0.72 | | | | |
| | | 60 A | 1j=125 C | 0.82 | 0.87 | | | | |
| Maximum reverse leakage current per leg | I _{RM} | T _J = 25 °C | V _R = Rated V _R | 7 | 75 | μΑ | | | |
| See fig. 2 | | T _J = 125 °C | VR = nateu VR | 7.2 | 20 | mA | | | |
| Typical junction capacitance per leg | C _T | V _R = 5 V _{DC} (test signal ran | = | 650 | pF | | | | |
| Typical series inductance per leg | L _S | Measured lead to lead 5 mm from package body | | | 7.5 | nH | | | |
| Maximum voltage rate of change | dV/dt | Rated V _R | = | 10 000 | V/µs | | | | |

Note

 $^{^{(1)}\,}$ Pulse width < 300 $\mu s,$ duty cycle < 2 %

| THERMAL - MECHANICAL SPECIFICATIONS | | | | | | | | |
|--|-------------|-----------------------------------|---|-------------|------------|--|--|--|
| PARAMETER | | SYMBOL | TEST CONDITIONS | VALUES | UNITS | | | |
| Maximum junction and storage temperature range |) | T _J , T _{Stg} | | - 55 to 175 | °C | | | |
| Maximum thermal resistance, | per leg | В | DC operation See fig. 4 | 1.2 | | | | |
| junction to case | per package | R_{thJC} | DC operation | 0.6 °C/W | | | | |
| Typical thermal resistance, case to heatsink | | R _{thCS} | Mounting surface, smooth and greased 0.25 | | | | | |
| Annyovimata wajaht | | | | 6 | g | | | |
| Approximate weight | | | | 0.21 | OZ. | | | |
| Mounting torque | minimum | | | 6 (5) | kgf · cm | | | |
| Mounting torque | maximum | | | 12 (10) | (lbf · in) | | | |
| Marking device | | | Case style 3 L TO-220AB | 60CTQ150 | | | | |






Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)

Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance ZthJC Characteristics (Per Leg)






Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)




Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)




Fig. 8 - Unclamped Inductive Test Circuit


Note

 $^{(1)}$ Formula used: T_C = T_J - (Pd + Pd_{REV}) x R_{th,JC}; Pd = forward power loss = I_{F(AV)} x V_{FM} at (I_{F(AV)}/D) (see fig. 6); Pd_{REV} = inverse power loss = V_{R1} x I_R (1 - D); I_R at V_{R1} = 80 % rated V_R



ORDERING INFORMATION TABLE





- 1 Vishay Semiconductors product
- 2 Current rating (60 = 60 A)
- 3 Circuit configuration

C = common cathode

4 - Package

T = TO-220

- 5 Schottky "Q" series
- 6 Voltage rating (150 = 150 V)
- 7 Environmental digit

-M3 = halogen-free, RoHS-compliant, and terminations lead (Pb)-free


| ORDERING INFORMATION (Example) | | | | | | | | | |
|---|----|------|-------------------------|--|--|--|--|--|--|
| PREFERRED P/N QUANTITY PER T/R MINIMUM ORDER QUANTITY PACKAGING DESCRIPTION | | | | | | | | | |
| VS-60CTQ150-M3 | 50 | 1000 | Antistatic plastic tube | | | | | | |


| LINKS TO RELATED DOCUMENTS | | | | | | | |
|--|--------------------------|--|--|--|--|--|--|
| Dimensions <u>www.vishay.com/doc?96154</u> | | | | | | | |
| Part marking information | www.vishay.com/doc?95028 | | | | | | |



3L TO-220AB

DIMENSIONS in millimeters and inches





Conforms to JEDEC® outline TO-220AB

| SYMBOL | MILLIM | IETERS | INCHES | | NOTES | NOTES | SYMBOL | MILLIN | IETERS | INC | HES | NOTES |
|--------|--------|--------|--------|-------|-------|-------|----------|--------|--------|-------|-------|-------|
| STMBOL | MIN. | MAX. | MIN. | MAX. | NOTES | | STIVIBOL | MIN. | MAX. | MIN. | MAX. | NOTES |
| Α | 4.25 | 4.65 | 0.167 | 0.183 | | | D2 | 11.68 | 12.88 | 0.460 | 0.507 | 6 |
| A1 | 1.14 | 1.40 | 0.045 | 0.055 | | | Е | 10.11 | 10.51 | 0.398 | 0.414 | 3, 6 |
| A2 | 2.50 | 2.92 | 0.098 | 0.115 | | | E1 | 6.86 | 8.89 | 0.270 | 0.350 | 6 |
| b | 0.69 | 1.01 | 0.027 | 0.040 | | | е | 2.41 | 2.67 | 0.095 | 0.105 | |
| b1 | 0.38 | 0.97 | 0.015 | 0.038 | 4 | | e1 | 4.88 | 5.28 | 0.192 | 0.208 | |
| b2 | 1.20 | 1.73 | 0.047 | 0.068 | | | H1 | 6.09 | 6.48 | 0.240 | 0.255 | 6, 7 |
| b3 | 1.14 | 1.73 | 0.045 | 0.068 | 4 | | L | 13.52 | 14.02 | 0.532 | 0.552 | |
| С | 0.36 | 0.61 | 0.014 | 0.024 | | | L1 | 3.32 | 3.82 | 0.131 | 0.150 | 2 |
| c1 | 0.36 | 0.56 | 0.014 | 0.022 | 4 | | ØΡ | 3.54 | 3.91 | 0.139 | 0.154 | |
| D | 14.85 | 15.35 | 0.585 | 0.604 | 3 | | Q | 2.60 | 3.00 | 0.102 | 0.118 | |
| D1 | 8.38 | 9.02 | 0.330 | 0.355 | | | | | | | | |

Notes

- ⁽¹⁾ Dimensioning and tolerancing as per ASME Y14.5M-1994
- (2) Lead dimension and finish uncontrolled in L1
- (3) Dimension D, D1, and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Dimension b1, b3, and c1 apply to base metal only
- Controlling dimensions: inches
- (6) Thermal pad contour optional within dimensions E, H1, D2, and E1
- (7) Outline conforms to JEDEC® TO-220, except D2 (minimum)



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.