



V1000

RS-A00-AFBA-G1

Features

- Fully modular cable design incorporates a single 1000W +12V output that delivers up to 83A.
- 80 PLUS Gold certified: up to 93% efficiency @ 50% load
- Silent 135 mm FDB fan for lower noise and longer lifespan
- Eight PCI-E 6+2 pin connectors to support high-end GPUs
- 100% high quality Japanese capacitor ensures performance and reliability.
- Reliable 5 year warranty

Packaging Information

















EAN Code	4719512041611
UPC Code	884102020797
Package Information	317 x 217 x 139 mm / 12.5 x 8.5 x 5.5 inches
Carton Dimensions	715 x 336 x 255 mm / 28.2 x 13.2 x 10 inches
Unit / Carton	5 pcs
Carton / Pallet	12 pcs

Specifications

Model Number	RS-A00-AFBA-G1
Type	Intel Form Factor ATX 12V V2.31
Dimensions	150 x 170 x 86mm / 5.9 x 6.7 x 3.4 inch
Input Voltage	90-264Vac (Auto Range)
Input Current	12 - 6A
Input Frequency Range	60 - 50Hz
PFC	Active PFC (>0.9)
Power Good Signal	100-500ms
Hold Up Time	>17ms
Efficiency	90% Typical
MTBF	>100,000 Hours
Protection	OVP/UVP/OPP/OTP/SCP
Output Capacity	1000W
Operation Temperature	0-40°C
Quality Certificates	CE/TUV/TUV-SUDNRTL/FCC/GOST/CC C/BSMI/C-tick/KCC
Fan	Silent FDB 135mm
Connectors	M/B 20+4 Pin x 1 CPU 4+4 Pin x 2 PCI-e 6+2 Pin x 8 SATA x 9 4 Pin Peripheral x 4 4 Pin Floppy x 1

AC INPUT	100-240V~ 12-6A 60-50Hz				
DC OUTPUT	+3.3V	+5V	+12V	-12V	+5Vsb
	25A	25A	83A	0.5A	3A
OUTPUT POWER	125W		996W	6W	15W
	1000W				



<p>1 x</p> <p>MB 24 pins</p> 	<p>600mm</p> 
<p>2 x</p> <p>CPU 4+4 pins</p> 	<p>680mm</p>  <p>680mm</p> 
<p>8 x</p> <p>PCI-e 6+2 pins</p> 	<p>600mm 100mm</p>  <p>600mm 100mm</p>  <p>600mm 100mm</p>  <p>600mm 100mm</p> 
<p>9 x</p> <p>SATA</p> 	<p>450mm 100mm 100mm</p>  <p>450mm 100mm 100mm</p>  <p>450mm 100mm 100mm</p> 
<p>4 x</p> <p>Peripherals</p>  <p>1 x</p> <p>Floppy</p> 	<p>450mm 100mm</p>  <p>450mm 100mm 100mm</p> 