



DEBUR AND BREAK SHARP EDGES

DO NOT SCALE DRAWING

REVISION



PART No.	ϕA	ϕB	C
TR NWE-34815-M2	4.9 +0.0 / -0.36	2.5 +0.18 / -0.0	0.35 ±0.05
TR NWE-34815-M2.5	6.5 +0.0 / -0.36	2.7 +0.18 / -0.0	0.50 ±0.05
TR NWE-34815-M3	7.0 +0.0 / -0.36	3.2 +0.18 / 0.0	0.50 ±0.05
TR NWE-34815-M4	9.0 +0.0 / 0.36	4.3 +0.18 / -0.0	0.80 ±0.10
TR NWE-34815-M5	10.0 +0.0 / -0.36	5.3 +0.18 / -0.0	1.00 ±0.10
TR NWE-34815-M6	12.0 +0.0 / -0.43	6.4 +0.22 / -0.0	1.60 ±0.20

A

DRAWN 16/07/14

NOTES



DESIGN RIGHT. TR FASTENINGS LTD, 2003
UNDER NO CIRCUMSTANCES MUST THIS
DRAWING BE COPIED OR DISCLOSED,
WITHOUT FIRST OBTAINING WRITTEN
AUTHORITY.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS
SURFACE FINISH:
TOLERANCES:

ISO 2768 m

NAME	DATE
DRAWN MARTIN ELLIOTT	16/07/14
CHK'D	
APPV'D	

CUSTOMER PART No

MATERIAL:

NYLON 66 UL94 -V2
NATURAL

HEAT TREATMENT

N/A

FINISH:

N/A

TITLE:


METRIC FLAT WASHER
(DIN 34815)

DWG NO.

TR NWE-34815-MX

A3

PROJECTION



SHEET 1 OF 1