


# 8900 Series Dissipative Rubber Mats and Rolls

8900 Series Dissipative Rubber Mats and Rolls meet ANSI/ESD S20.20 required limit and the recommendation of work surface standard ANSI/ESD S4.1. The product is constructed using a top color layer of static dissipative neoprene rubber laminated to a bottom black layer of conductive neoprene rubber. Both layers are made from vulcanized synthetic rubber, which offers resistance to oil, grease and most common solvents. They offer increased resistance to heat and hot solder as compared to vinyl or olefin materials. Non-standard sizes are available on a custom order basis. Compatible with Continuous or Constant Monitors.



Made in the United States of America



8900 Table Mat Kit shown with included hardware

Available in Blue or Gray

## Table Mat Kit Item Numbers

Size	Blue	Gray
2' x 4' (0.6 m x 1.2 m)	<a href="#">8900</a>	<a href="#">8901</a>

### Table Mat Kit Includes:

- 1 Table Mat, size as specified
- 1 [3048](#) Wrist Strap Grounding System
- 2 [3034](#) Snap Fasteners (installed)

## Table Roll Item Numbers

Size	Blue	Gray
24" x 50' (0.6 m x 15.2 m)	<a href="#">8902</a>	
30" x 50' (0.7 m x 15.2 m)	<a href="#">8903</a>	
36" x 50' (0.9 m x 15.2 m)	<a href="#">8904</a>	
48" x 50' (1.2 m x 15.2 m)	<a href="#">8905</a>	<a href="#">8906</a>

### Table Roll Includes:

- 1 Table Roll, size as specified

Electrical Properties	Typical Value	Test Method
Color Top Layer Resistances		
Surface to Ground (Rtg)	1 x 10 <sup>6</sup> to < 1 x 10 <sup>8</sup> ohms	ANSI/ESD S4.1 & ESD TR53
Surface to Surface (Rtt)	1 x 10 <sup>6</sup> to < 1 x 10 <sup>8</sup> ohms	ANSI/ESD S4.1 & ESD TR53
Conductive Bottom Layer Resistance		
Surface to Surface (Rtt)	< 1 x 10 <sup>4</sup> ohms	ANSI/ESD S4.1 & ESD TR53

Physical Properties	Typical Value
Material	Dual-layer rubber material
Thickness*	0.065" (1.7 mm)
Hardness	70 +/- 5 Shore A
Tolerance	Width +/- 0.250" Length +/- 0.250" Thickness +/- 10%
Color*	Blue, Gray (Top) Black (Bottom)
Texture*	Slight embossed

Other Properties	Typical Value
Heat Resistance	Does not melt or burn when coming into contact with hot solder and soldering irons
Chemical Resistance	Resistance to degradation by inorganic acids, organic acids, reducing agents, aliphatic hydrocarbons, mineral oil, aldehydes, and amines

**Cutting Material:** Matting materials have a tendency to shrink slightly when first unrolled. In applications where length is critical, allow the material to condition for at least 4 hours before cutting to size. Always using care trim with a sharp knife or razor blade.

**Grounding:** If the material is used on top of an already properly grounded surface, grounding hardware may not be necessary. Where no properly grounded surface is available, grounding hardware is required to provide a path-to-ground.

\*Color, texture and thickness may vary between lots and mills.

### RoHS 3, REACH, and Conflict Minerals Statement

None of the RoHS 3 restricted materials or REACH substances of very high concern as of 2018/08/01, or Conflict Minerals are intentionally added in manufacturing this product. Ref: European Union Directive (EU) 2015/853 amending Annex II of the RoHS 2 Directive 2011/65/EU and Regulation (EC) No. 1907/2006/CE. See [SCS Warranty, Limitation of Liability and Remedies](#)

Specifications and procedures subject to change without notice.

## 8900 SERIES DISSIPATIVE RUBBER MATS AND ROLLS

926 JR Industrial Drive, Sanford, NC 27332  
 WEB SITE: [StaticControl.com](http://StaticControl.com)  
 PHONE (919) 718-0000

**DRAWING NUMBER**  
8900

**DATE**  
August 2018

