

Raise3D Premium PLA Technical Data Sheet

Raise3D Premium PLA is a premium PLA designed for all desktop FDM/FFF printers. It ensures consistent extrusion and prevents nozzle jams.

Physical Properties

Property	Testing Method	Typical Value
Density(g/cm ³ at 21.5 °C)	ASTM D792 (ISO 1183, GB/T 1033)	1.17-1.24
Glass transition temperature(°C)	DSC, 10 °C/min	50-60
Softening temperature of filament(for 1.75 mm; °C)	Custom method	146-150
Melt index(g/10 min)	210 °C, 2.16 kg	7-11
Moisture content ¹ (%)	Thermogravimetric	≤0.1%
Odor	/	Almost odorless
Solubility	/	Insoluble in water; soluble in chloroform, toluene, and tetrahydrofuran(THF)

Note:

1.For newly opened filaments; filaments may absorb higher levels of moisture during use.

Mechanical Properties¹

Property	Testing Method	Typical Value
Young's modulus(MPa)	ASTM D638 (ISO 527, GB/T 1040)	2636±330
Tensile strength(MPa)	ASTM D638 (ISO 527, GB/T 1040)	46.6±0.9
Elongation at break(%)	ASTM D638 (ISO 527, GB/T 1040)	1.90±0.21
Bending modulus(MPa)	ASTM D790 (ISO 178, GB/T 9341)	3283±132



Bending strength(MPa)	ASTM D790 (ISO 178, GB/T 9341)	85.1±2.9
Impact strength(KJ/m ²)	ASTM D256 (ISO 179, GB/T 1043)	2.68±0.16

Note:

- All testing specimens were printed using a Raise3D N2 under the following conditions:
Printing temperature = 230 °C, printing speed = 90 mm/s, number of shells = 2, and 100% infill.

Testing Geometries




Fig 1. Tensile testing specimen




Fig 2. Flexural testing specimen




Fig 3. Impact testing specimen

Disclaimer



The typical values presented in this data sheet are intended for reference and comparison purposes only. They should not be used for design specifications or quality control purposes. Actual values may vary significantly with printing conditions. Enduse performance of printed parts depends not only on materials, but also on part design, environmental conditions, printing conditions, etc. Product specifications are subject to change without notice.

Each user is responsible for determining the safety, lawfulness, technical suitability, and disposal/recycling practices of Raise3D materials for the intended application. Raise3D makes no warranty of any kind, unless announced separately, to the fitness for any particular use or application. Raise3D shall not be made liable for any damage, injury or loss induced from the use of Raise3D materials in any particular application.



Part number	Colour	Diameter	Weight
PLA			
10845	White	1.75mm	1kg
10846	Black	1.75mm	1kg
10847	Grey	1.75mm	1kg
10848	Golden	1.75mm	1kg
10849	Bronze	1.75mm	1kg
Premium PLA			
10837	White	1.75mm	1kg
10838	Black	1.75mm	1kg
10839	Red	1.75mm	1kg
10840	Orange	1.75mm	1kg
10841	Yellow	1.75mm	1kg
10842	Blue	1.75mm	1kg
Premium ABS			
10843	White	1.75mm	1kg
10844	Black	1.75mm	1kg